

OL 2008



GENERAL INDUSTRY

Air and water transportation



APPLICATIONS

For transportation of water and air.
Non-reinforced hose for low pressure.

ADVANTAGES

- ¹ Food grade quality.
- ¹ Unreinforced.
- ¹ Transparent.
- ¹ DEHP-free.

TECHNICAL DESCRIPTION

Inner tube: PVC, transparent, smooth.

Cover: PVC, transparent, smooth.

Temperature range: -10 °C to +60 °C.

STANDARD/APPROVAL

Meets EU directive 10/2011/CE A, B, C, D.





GENERAL INDUSTRY

OL 2008



ID mm	WALL THICKNESS mm	OD mm	LENGTH m	TYPE	ARTICLE NUMBER	STOCK (1) or min. order m
2.0	1	4.0	100	300 m/box	1466940	300
3.0	1	5.0	50	300 m/box	0894923	1
4.0	1	6.0	50	300 m/box	0071128	1
4.0	1.5	7.0	50	250 m/box	0071350	1
5.0	1	7.0	50	250 m/box	1461320	1
5.0	1.5	8.0	50	300 m/box	0071417	1
5.0	2	9.0	100	300 m/box	1461330	∞
6.0	1.5	9.0	50	300 m/box	0071341	1
6.0	2	10.0	50	300 m/box	0071129	300
7.0	1.5	10.0	50	300 m/box	0894980	1
8.0	1.5	11.0	50	200 m/box	0872234	1
8.0	2	12.0	50	300 m/box	0872440	1
9.0	2	13.0	50	200 m/box	1466950	1
10.0	3	16.0	50		0071181	1
10.0	2	14.0	50		1461380	∞
12.0	2	16.0	50		0872390	1
12.0	3	18.0	50		0872382	50
14.0	2	18.0	50		1461400	1
15.0	2	19.0	25		1588550	∞
16.0	2.5	21.0	50		5008010	1
18.0	2.5	23.0	50		1446300	∞
19.0	3.5	26.0	50		5008008	1
20.0	3	26.0	50		0070523	∞
25.0	3	31.0	50		1461490	1
25.0	4	33.0	50		5008009	1
30.0	4	38.0	50		1461520	∞
32.0	5	42.0	25		1404990	1
38.0	5	48.0	25		1461540	∞
60.0	5	70.0	25		5016344	∞

Tolerance on length: $\pm 1\%$ (ISO 1307 Standard).

∞ Upon availability.

