

# TR 20080



## GENERAL INDUSTRY

Air



### APPLICATIONS

A high quality PVC hose for all air tools.

Very flexible, weatherproof and durable.

Better cooling flexibility than standard PVC tubing.

### ADVANTAGES

- Very flexible hose, good weather resistance and durability.
- Good cold flexibility.
- Good resistance to oils and solvents inside as well as outside (see chemical resistance list for PVC).

### TECHNICAL DESCRIPTION

Inner tube: PVC.

Reinforcement: synthetic textile, polyester.

Cover: PVC, beige, smooth.

Temperature range: -15°C to +60°C.



**GENERAL INDUSTRY****TR 20080**

ID mm	WALL THICKNESS mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK ( ) or min. order m
6.3	2.35	11.0	20	60	22	0.08	50	2259190	50
8.0	2.5	13.0	20	60	28	0.1	50	2259200	50
10.0	2.75	15.5	20	60	35	0.14	50	2259210	1
12.7	3.15	19.0	20	60	45	0.2	50	2259220	1
16.0	3.5	23.0	20	60	56	0.28	50	2259230	100
19.0	3.75	26.5	20	60	66	0.35	50	2259240	1
25.0	4.25	33.5	20	60	87	0.5	50	2259250	1

Tolerance on length:  $\pm 1\%$  (ISO 1307 Standard).

**TRELLEBORG**

[WWW.TRELLEBORG.COM/FLUIDHANDLING](http://WWW.TRELLEBORG.COM/FLUIDHANDLING)