

TEGUFLEX® P LPG



**CHEMICALS &
PHARMACEUTICALS**



AUFBAU

Seele: schwarz.

Decke: schwarz.

Einsatztemperatur: -25°C bis 110°C.



TRELLEBORG IZARRA
IZARRA-ALAVA-SPAIN
Batch number - Working pressure - Testing pressure - T MAX/MIN - DN - Month/Year

CE 0056
MOD: H TEGUFLEX LPG TRELLEBORG

 CHEMICALS & PHARMACEUTICALS			TEGUFLEX® P LPG								
INNEN-Ø mm	PN	BETRIEBS- DRUCK bar	BERST- DRUCK bar	BL m	COMPRESSIO N mm	ELONGATION mm	LATERAL mm	ANGULAR °	WITHOUT SUPPORT RING BAR	ARTIKEL-NR.	LAGER (1) oder MB Stück
50.0	40	25	100	130	30	20	20	35	0.7	5603746	∅
80.0	40	25	100	130	30	20	20	30	0.5	5603747	∅
∅ Je nach Lagerbestand.											

Digital version



WWW.TRELLEBORG.COM/FLUIDHANDLING