

TEGUFLEX® P PURPLE



**CHEMICALS &
PHARMACEUTICALS**



AUFBAU

Seele: FKM, schwarz.

Decke: FKM, schwarz.

Einsatztemperatur: -15°C bis 150°C.



TRELLEBORG IZARRA
IZARRA-ALAVA-SPAIN
Batch number - Working pressure - Testing pressure - T MAX/MIN - DN - Month/Year

CE 0056
MOD: H

TEGUFLEX P



TRELLEBORG

 CHEMICALS & PHARMACEUTICALS			TEGUFLEX® P PURPLE				  				
INNEN-Ø mm	PN	BETRIEBS- DRUCK bar	BERST- DRUCK bar	BL m	COMPRESSIO N mm	ELONGATION mm	LATERAL mm	ANGULAR °	WITHOUT SUPPORT RING BAR	ARTIKEL-NR.	LAGER (1) oder MB Stück
32.0	10/16	16	50	130	30	20	20	35	0.8	TP0032VIVI0001	1
50.0	10/16	16	50	130	30	20	20	35	0.7	5603826	☒
65.0	10/16	16	50	130	30	20	20	30	0.6	5604256	☒
80.0	10/16	16	50	130	30	20	20	30	0.5	5604128	☒
100.0	10/16	16	50	130	30	20	20	25	0.5	5604127	☒
100.0	20	16	50	130	30	20	20	25	0.5	TP0100VIVI0002	☒
125.0	10/16	16	50	130	30	20	20	25	0.4	5604257	☒
150.0	10/16	16	50	130	30	20	20	15	0.3	TP0150VIVI0001	☒
200.0	10	10	30	130	30	20	20	15	0.3	5603923	☒
200.0	16	10	30	130	30	20	20	15	0.3	TP0200VIVI0002	☒
250.0	10	10	30	130	30	20	20	10	0.2	5603924	☒
300.0	10	10	30	130	30	20	20	10	0.2	5603925	☒
☒ Je nach Lagerbestand											

Digital version



WWW.TRELLEBORG.COM/FLUIDHANDLING