

TEGUFLEX® W HP



GENERAL INDUSTRY



AUFBAU

Seele: EPDM special, schwarz.

Decke: EPDM special, schwarz.

Einsatztemperatur: -35°C bis 130°C.



TRELLEBORG IZARRA
IZARRA-ALAVA-SPAIN
Batch number - Working pressure - Testing pressure - T MAX/MIN - DN - Month/Year



**GENERAL INDUSTRY****TEGUFLEX® W HP**

INNEN-Ø mm	PN	BETRIEBS- DRUCK bar	BERST- DRUCK bar	BL m	COMPRESSIO N mm	ELONGATION mm	LATERAL mm	ANGULAR °	WITHOUT SUPPORT RING BAR	ARTIKEL-NR.	LAGER (1) oder MB Stück
40.0	10/16	16	50	150	30	20	20	35	0.8	5604073	☒
50.0	10/16	16	50	150	30	20	20	35	0.8	5603250	☒
65.0	10/16	16	50	150	30	20	20	30	0.8	0380401	☒
80.0	10/16	16	50	150	30	20	20	30	0.5	5013942	☒
100.0	10/16	16	50	150	30	20	20	25	0.5	TW0100HHP0002	☒
125.0	10/16	16	50	150	30	20	20	15	0.5	TW0125HHP0001	☒
150.0	10/16	16	50	150	30	20	20	15	0.5	5490284	☒
200.0	10	10	30	200	30	20	20	15	0.3	5010769	☒
200.0	20	10	30	200	30	20	20	15	0.3	TW0200HHP0002	☒
300.0	10	10	30	200	30	20	20	10	0.3	TW0300HHP0002	☒
350.0	10	10	30	200	30	20	20	10	0.3	S381208	☒
350.0	16	10	30	200	30	20	20	10	0.3	5012203	☒
400.0	10	10	30	200	30	20	20	10	0.3	5604045	☒
500.0	10	10	50	200	30	20	20	10	0.3	0380130	☒

☒ Je nach Lagerbestand.

Digital version

WWW.TRELLEBORG.COM/FLUIDHANDLING