

TEGUFLEX® W DW



FOOD & BEVERAGE



CARACTERISTIQUES TECHNIQUES

Tube : noir.

Revêtement : noir.

Température : -25 °C à 90 °C.



TRELLEBORG IZARRA
IZARRA-ALAVA-SPAIN
Batch number - Working pressure - Testing pressure - T MAX/MIN - DN - Month/Year

CE 0056 TEGUFLEX DW TRELLEBORG MOD: H

**FOOD & BEVERAGE****TEGUFLEX® W DW**

DIAMÈTRE INTÉRIEUR mm	PN	PRESSION DE SERVICE bar	PLNE bar	BL m	COMPRESSIO N mm	ELONGATION mm	LATERAL mm	ANGULAR °	WITHOUT SUPPORT RING BAR	CODE ARTICLE	STOCK (1) ou min. de cde pièce
65.0	16	16	50	150	30	20	20	30	0.8	TW0065RW2RW2000	✕
400.0	16	10	30	200	30	20	20	10	0.3	5602680	✕

✕ Selon disponibilité.

Digital version

WWW.TRELLEBORG.COM/FLUIDHANDLING