

TEGUFLEX® W PURPLE



**CHEMICALS &
PHARMACEUTICALS**



AUFBAU

Seele: FKM, schwarz.

Decke: FKM, schwarz.

Einsatztemperatur: -15°C bis 150°C.



TRELLEBORG IZARRA
IZARRA-ALAVA-SPAIN
Batch number - Working pressure - Testing pressure - T MAX/MIN - DN - Month/Year

CE 0056
MOD: H

TEGUFLEX W



TRELLEBORG

 CHEMICALS & PHARMACEUTICALS		TEGUFLEX® W PURPLE 									
INNEN-Ø mm	PN	BETRIEBS- DRUCK bar	BERST- DRUCK bar	BL m	COMPRESSIO N mm	ELONGATION mm	LATERAL mm	ANGULAR °	WITHOUT SUPPORT RING BAR	ARTIKEL-NR.	LAGER (L) oder MB Stück
80.0	10/16	16	50	150	30	20	20	30	0.5	0507564	∅
∅ Je nach Lagerbestand.											

Digital version



WWW.TRELLEBORG.COM/FLUIDHANDLING