

AIR 40



GENERAL INDUSTRY

Air and water



APPLICATIONS

Heavy duty air hose for use in mines, construction and industrial applications.

TECHNICAL DESCRIPTION

Inner tube: oil resistant SBR, black, smooth.

Reinforcement: steel wire braided.

Cover: weather resistant SBR, yellow, fabric impression.

Temperature range: -30°C to +80°C.

**GENERAL INDUSTRY****AIR 40**

ID mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK (1) or min. order m
13.0	25.0	40	160	100	0.52	40	5503634	560
19.0	32.0	40	160	180	0.79	40	5503635	560
25.0	38.0	40	160	200	1.04	40	5503636	560
51.0	66.0	40	160	410	2.12	40	5503637	400
76.0	94.0	40	160	600	3.73	40	5503638	200

Tolerance on length: $\pm 1\%$ (ISO 1307 Standard).

