

AQUA 10 FG



GENERAL INDUSTRY

Coolant hoses



APPLICATIONS

Water cooling hose with glass fibre cover.

TECHNICAL DESCRIPTION

Inner tube: non-conductive EPDM, white, smooth.

Reinforcement: synthetic textile.

Cover: glass fibre fabric, beige.

Temperature range: -30 °C to +100 °C.
+550 °C heat radiation.

Electrical properties: $R > 10^8 \Omega/m$.



**GENERAL INDUSTRY****AQUA 10 FG**

ID mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK (1) or min. order m
19.0	31.0 ±1	10	30	160	0.64	40	5503640	160
25.0	37.0 ±1	10	30	200	0.83	40	5503641	200
38.0	52.0 ±1.2	10	30	310	1.3	40	5503642	200
51.0	65.0 ±1.2	10	30	450	1.75	40	5503643	160
63.0	79.0 ±1.2	10	30	560	2.55	40	5503644	160
102.0	119.0 ±1.2	10	30	1020	3.97	40	5503639	160

Tolerance on length: ±1% (ISO 1307 Standard).

**TRELLEBORG**

WWW.TRELLEBORG.COM/FLUIDHANDLING