

ABRA 10 SLURRY



MINING & QUARRIES

Abrasive materials hydraulic and pneumatic handling



APPLICATIONS

Hydraulic suction and discharge of abrasive products.

TECHNICAL DESCRIPTION

Inner tube: wear resistant NR, black, smooth.

Reinforcement: synthetic textile with embedded steel helix.

Cover: wear resistant NR/SBR, black, smooth fabric impression.

Temperature range: -30°C to +70°C.

Electrical properties: conductive tube, $R < 1 \text{ M}\Omega/\text{m}$.

COUPLINGS/FITTINGS

Special half shelves coupling.

50-200mm



250-400mm



**MINING & QUARRIES****ABRA 10 SLURRY**

ID mm	OD mm	TUBE THICKNESS mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	MAX. VACUUM bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK (1) or min. order m
50.0	70.0	5	10	30	0.9	250	3	20	5513746	1
75.0	96.0	5	10	30	0.9	375	4	20	5513747	1
100.0	123.0	5	10	30	0.9	500	6	20	5513748	1
125.0	150.0	5	10	30	0.9	650	7.5	20	5513749	1
150.0	174.0	5	10	30	0.9	900	8	20	5513750	1
200.0	230.0	6	10	30	0.9	1400	12	10	5513751	1
250.0	282.0	6	5	15	0.9	1750	17	10	5513752	40
300.0	336.0	8	5	15	0.9	2100	22	10	5513753	40
350.0	386.0	8	5	15	0.9	2750	26	10	5513754	1
400.0	436.0	8	5	15	0.9	3500	30	10	5513755	10

Tolerance on length: $\pm 1\%$ (ISO 1307 Standard).

