

AQUA 10



AGRICULTURE

Water
Discharge applications



APPLICATIONS

Water delivery hose (lay-flat type from ID 51), for irrigation, industrial or waste water.

TECHNICAL DESCRIPTION

Inner tube: SBR, black, smooth.

Reinforcement: synthetic textile.


Cover: SBR, black, fabric impression.

Temperature range: -30°C to +80°C.



TRELLEBORG

AQUA 10



 AGRICULTURE		AQUA 10					
ID mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK (1) or min. order m
25.0	33.0 ±1	10	30	0.49	40	5503679	200
32.0	40.0 ±1	10	30	0.61	40	5503681	200
38.0	46.0 ±1	10	30	0.74	40	5503682	1
51.0	59.0 ±1	10	30	0.97	40	5503683	1
63.0	71.0 ±1	10	30	1.18	40	5503684	240
76.0	84.0 ±1	10	30	1.37	40	5503685	1
102.0	111.0 ±1	10	30	2	40	5503674	1
127.0	137.0 ±1	10	30	2.89	40	5503675	120
152.0	161.0 ±1	10	30	3.28	40	5503676	1
203.0	215.0 ±1	10	30	6.1	40	5503677	1
Tolerance on length: ±1% (ISO 1307 Standard).							

