

MULTI 20 HOT



GENERAL INDUSTRY

Hot water and multipurpose
chemicals



APPLICATIONS

Multi-purpose hose, with very good ageing. Suitable for air, cold and hot water and many other chemical products.

TECHNICAL DESCRIPTION



Inner tube: EPDM, black, smooth.

Reinforcement: synthetic textile.

Cover: EPDM, black, smooth.

Temperature range: -30°C to +100°C.

Electrical properties: conductive tube and cover, $R \leq 1 \text{ M}\Omega/\text{lg}$ ($R \leq 10^6 \Omega/\text{lg}$).

 GENERAL INDUSTRY			MULTI 20 HOT					
ID mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK () or min. order m
10.0	17.0	20	80	60	0.19	40	5513861	
13.0	21.0	20	80	80	0.28	40	5513862	
16.0	24.0	20	80	100	0.33	40	5513863	
19.0	28.0	20	80	115	0.43	40	5513864	
25.0	35.0	20	80	150	0.61	40	5513865	
Tolerance on length: ±1% (ISO 1307 Standard).								