

MULTI 25 OIL



GENERAL INDUSTRY

Multipurpose oil



APPLICATIONS

Versatile hose for diesel, mineral oil and grease with aromatic content <50%.

TECHNICAL DESCRIPTION

Inner tube: NBR, black, smooth.

Reinforcement: synthetic textile.

Cover: NBR, black, smooth.

Temperature range: -30 °C to +100 °C.

Electrical properties: conductive tube and cover, $R \leq 1 \text{ M}\Omega/\text{lg}$ ($R \leq 10^6 \Omega/\text{lg}$).

 GENERAL INDUSTRY			MULTI 25 OIL					
ID mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK (1) or min. order m
6.0	13.0	25	80	40	0.14	40	5513852	1
8.0	15.0	25	80	50	0.17	40	5513853	1
10.0	17.0	25	80	60	0.19	40	5513854	1
13.0	21.0	25	80	80	0.28	40	5513855	1
16.0	25.0	25	80	100	0.33	40	5513856	1
19.0	28.0	25	80	120	0.43	40	5513857	1
25.0	35.0	25	80	150	0.61	40	5513858	1
Tolerance on length: $\pm 1\%$ (ISO 1307 Standard).								

