BERGALAV

FOOD & BEVERAGE

Food industry
Cleaning



APPLICATIONS

For hot water cleaning in food processing plants with possible occasionnal use with steam up to 160°C.

ADVANTAGES

- Highly flexible.
- Specially adapted to keep round on reels.
- Contains no phthalate.

TECHNICAL DESCRIPTION

Inner tube: food grade quality EPDM, white, smooth.
Reinforcement: synthetic textile.
Cover: weather resistant EPDM, blue, smooth.
Temperature range: -30°C to +160°C.

STANDARD/APPROVAL

EU regulations No. 1935/2004, 2023/2006.	EU
FDA regulation No. 21 CFR 177.2600.	FDA
French legislation.	RF
All relevant migrations tests (France and FDA) were performed by the French institute of Poitiers (IANESCO) and confirmed compliant.	

COUPLINGS/FITTINGS

Specially designed fittings are available, please contact us for further information in order to get optimum connections.

COMPLEMENTARY INFORMATION

Please refer to our cleaning guidelines, available upon request and from our website.



and embossed: week/year - batch number

FOOD & BEVERAGE | **BERGALAV**



ID mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK (l) or min. order m
10.0 ±0.6	18.0 ±0.7	10	30	75	0.25	20	5501308	l
10.0 ±0.6	18.0 ±0.7	10	30	75	0.25	40	5501309	l
13.0 ±0.6	22.0 ±0.7	10	30	95	0.35	20	5500857	l
13.0 ±0.6	22.0 ±0.7	10	30	95	0.35	40	5500858	l
16.0 ±0.7	25.0 ±0.8	10	30	110	0.41	20	5500859	l
16.0 ±0.7	25.0 ±0.8	10	30	110	0.41	40	5500860	l
19.0 ±0.8	29.0 ±0.9	10	30	135	0.54	20	5500861	l
19.0 ±0.8	29.0 ±0.9	10	30	135	0.54	40	5500862	l
25.0 ±1.0	36.0 ±1.0	10	30	180	0.74	20	5500863	l
25.0 ±1.0	36.0 ±1.0	10	30	180	0.74	40	5500864	l

Tolerance on length: ±1% (ISO 1307 Standard).