TRELLJET 580

CONSTRUCTION & INFRASTRUCTURE

Water
High pressure jetting



APPLICATIONS

Specially designed for professional and industrial high pressure cleaning.

Efficient for machines, vehicles, floors, public areas, facades, etc.

The non-staining cover is also an advantage for use in food industry and public baths.

Suitable for mobile pressure washers, fixed installations and reel mounted applications.

ADVANTAGES

- Non-staining smooth cover.
- Oil, detergent, wear and weather resistant.
- High working pressure.
- High temperature resistance.
- Light weight, flexible and kink resistant.
- Long service life.

TECHNICAL DESCRIPTION

Inner tube: NBR/SBR, black, smooth.
Reinforcement: steel, two braids.
Cover: SBR/NBR, blue, smooth.
Temperature range: -40°C to +150°C.

COUPLINGS/FITTINGS

Specially designed fittings are available, please contact us for further information in order to get optimum connections.


COMPLEMENTARY INFORMATION

50% of the volume in each delivery will be random lengths, shortest length of 10m, at least 50% will be in fixed length mentioned in the table.



CONSTRUCTION & INFRASTRUCTURE

TRELLJET 580



ID mm	WALL THICKNESS mm	OD mm	REINF. DIAMETER mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK (l) or min. order m
7.9 +0.6/-0.2	3.55	15.0 ±0.7	12.7 ±0.3	650	1600	65	0.31	100	2910310	l
9.5 +0.6/-0.2	3.8	17.4 ±0.7	14.9 ±0.3	650	1600	70	0.38	100	2910370	l
12.7 +0.8/-0.4	3.75	20.6 ±0.8	18.1 ±0.3	500	1200	70	0.47	100	2910420	l

Tolerance on length: ±1% (ISO 1307 Standard).

Digital version

TRELLEBORG

WWW.TRELLEBORG.COM/FLUIDHANDLING