FP 2007

AQUACULTURE

Farm
Pumping fish



APPLICATIONS

Used for pumping fish in fish farms and fish processing factories.

ADVANTAGES

- Flexible hose design providing optimum characteristics for this application.
- Withstands rough handling.
- Without helix for discharge applications.

TECHNICAL DESCRIPTION

Inner tube: wear resistant SBR/NBR, black, smooth.
Reinforcement: synthetic textile.
Cover: weather resistant SBR/NBR, black, fabric impression.
Temperature range: -40°C to +80°C.

COMPLEMENTARY INFORMATION

Other lengths available on request.



and in opposite:



AQUACULTURE | **FP 2007**



ID inch	ID mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK (t) or min. order m
10	254.0	261.0 ±1.5	2	7	3.05	40	5010364	40
12	305.0	312.0 ±1.5	2	7	3.66	30	0594432	30
12	305.0	312.0 ±1.5	2	7	3.66	40	0208009	40
14	355.0	362.0 ±1.5	2	7	4.25	30	0594424	30
14	355.0	362.0 ±1.5	2	7	4.25	40	0208025	40

Tolerance on length: ±1% (ISO 1307 Standard).

Digital version

TRELLEBORG

WWW.TRELLEBORG.COM/FLUIDHANDLING