PROJECTOR 120

CONSTRUCTION & INFRASTRUCTURE

Spraying



APPLICATIONS

For spraying of wet mortar, mixed concrete and other wet products.

Used as a service hose between pump and nozzle in transporting plaster, grout and ready mixed concrete.

ADVANTAGES

- High working pressure.
- Light weight, flexible and easy to handle.
- Abrasion resistant tube.
- Non-staining white cover avoids traces on walls and floors.

TECHNICAL DESCRIPTION

Inner tube: wear resistant NR, black, smooth.
Reinforcement: synthetic textile.
Cover: wear and weather resistant SBR, black, fabric impression.
Temperature range: -30°C to +70°C.
Electrical properties: antistatic tube.
Special properties: abrasion resistance of tube <40mm³ according to ISO 4649.


COMPLEMENTARY INFORMATION

13.3m lengths available on request, min. order is three pieces and by multiple of three.
Other wall thickness and/or bursting pressure on request.



CONSTRUCTION & INFRASTRUCTURE

PROJECTOR 120



ID mm	WALL THICKNESS mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK (l) or min. order m
19.0	6	31.0	40	120	150	0.27	40	5513550	200
25.0	7	39.0	40	120	200	0.85	40	5513551	l
30.0	7	44.0	40	120	240	1	40	5513552	200
32.0	8	48.0	40	120	260	1.22	40	5513553	l
35.0	7	49.0	40	120	280	1.12	40	5513554	l
38.0	8	54.0	40	120	300	1.45	40	5513564	l
40.0	7.5	55.0	40	120	310	1.53	40	59006802	200
50.0	9	68.0	40	120	410	2.01	20	59006804	l
50.0	9	68.0	40	120	410	2.01	40	5513557	l
60.0	10	80.0	40	120	480	2.66	40	5513558	160
63.0	10	83.0	40	120	500	2.77	40	5513559	160
65.0	10	85.0	40	120	520	2.84	20	59006805	200
65.0	10	85.0	40	120	520	2.84	40	5513560	l
76.0	10	96.0	40	120	600	3.31	40	5513561	160
90.0	12	114.0	40	120	720	4.45	20	59006806	l
102.0	14	130.0	40	120	800	5.67	40	5513563	160

Tolerance on length: ±1% (ISO 1307 Standard).

TRELLEBORG