AQUA 10 SD

AGRICULTURE

Water
Suction applications




APPLICATIONS

Water suction and delivery hose used for industrial water, waste water and agricultural equipment.

TECHNICAL DESCRIPTION

Inner tube: SBR, black, smooth.
Reinforcement: synthetic textile with embedded steel helix.
Cover: SBR, black, fabric impression.
Temperature range: -30°C to +80°C.



AGRICULTURE | **AQUA 10 SD**



ID mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	MAX. VACUUM bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK (ι) or min. order m
25.0	35.0 ±1	10	30	0.9	100	0.71	40	5503700	ι
32.0	42.0 ±1	10	30	0.9	120	1.01	40	5503701	ι
38.0	48.0 ±1	10	30	0.9	160	1.19	40	5503702	ι
51.0	63.0 ±1	10	30	0.9	200	1.72	40	5503703	ι
63.0	75.0 ±1	10	30	0.9	245	2.23	20	59007854	ι
63.0	75.0 ±1	10	30	0.9	245	2.23	40	5503704	160
76.0	88.0 ±1	10	30	0.9	320	2.57	20	59007855	ι
76.0	88.0 ±1	10	30	0.9	320	2.57	40	5503705	160
90.0	103.0 ±1.2	10	30	0.9	360	3.36	20	59007856	160
90.0	103.0 ±1.2	10	30	0.9	360	3.36	40	5503706	160
102.0	116.0 ±1.2	10	30	0.9	410	4.05	20	59007857	ι
102.0	116.0 ±1.2	10	30	0.9	410	4.05	40	5503695	ι
127.0	143.0 ±1.2	10	30	0.9	510	5.82	20	59007858	¤
127.0	143.0 ±1.2	10	30	0.9	510	5.82	40	5503696	ι
152.0	169.0 ±1.2	10	30	0.9	610	7.66	20	59007859	ι
152.0	169.0 ±1.2	10	30	0.9	610	7.66	40	5503697	¤
203.0	225.0 ±1.6	10	30	0.8	1000	13.28	20	59007860	ι
203.0	225.0 ±1.6	10	30	0.8	1000	13.28	40	5503698	ι
254.0	276.0 ±1.6	10	30	0.8	1270	19.17	20	59007861	¤

Tolerance on length: ±1% (ISO 1307 Standard). ¤ Upon availability.

TRELLEBORG

WWW.TRELLEBORG.COM/FLUIDHANDLING