MULTI 10 OIL

GENERAL INDUSTRY

Multipurpose oil




APPLICATIONS

Versatile hose for diesel, mineral oil and grease with aromatic content <50%.

TECHNICAL DESCRIPTION

Inner tube: NBR, black, smooth.
Reinforcement: synthetic textile.
Cover: NBR, black, smooth.
Temperature range: -30 °C to +100 °C.
Electrical properties: conductive tube and cover, R≤1MΩ/lg ($R \leq 10^6 \Omega$/lg).



GENERAL INDUSTRY | **MULTI 10 OIL**



ID mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK (▯) or min. order m
6.0	12.0	10	40	45	0.13	40	5513845	3200
8.0	14.0	10	40	55	0.14	40	5513846	¤
10.0	17.0	10	40	60	0.21	40	5513847	¤
13.0	20.0	10	40	80	0.26	40	5513848	2400
16.0	24.0	10	40	100	0.34	40	5513849	2960
19.0	27.0	10	40	120	0.41	40	5513850	¤
25.0	34.0	10	40	150	0.6	40	5513851	2280

Tolerance on length: ±1% (ISO 1307 Standard). ¤ Upon availability.

TRELLEBORG