VK 2000

GENERAL INDUSTRY

Exhaust and ventilation

APPLICATIONS

Extraction of air, smoke (also corrosive), dust and light particles.

Also used as cable protection.

ADVANTAGES

- A flexible PVC hose with a strong PVC spiral.
- Kink resistant.

TECHNICAL DESCRIPTION

Inner tube: PVCsmooth.
Reinforcement: impact resistant PVC helix.
Cover: PVC, blue, corrugated.
Temperature range: -10°C to +50°C.
Electrical properties: non conductive material.

GENERAL INDUSTRY

VK 2000

ID mm	WALL THICKNESS mm	OD mm	WORKING PRESSURE bar	BENDING RADIUS mm	LENGTH m	ARTICLE NUMBER	STOCK (ι) or min. order m
25.0	0.6	27.3	0.8	40	30	5109000	ι
38.1	0.7	40.8	0.7	40	30	5109010	60
50.0	0.7	52.9	0.7	90	30	5109020	¤
63.5	0.7	66.9	0.6	100	30	5109025	60
76.2	0.7	79.9	0.5	120	30	5109030	ι
90.0	0.8	94.1	0.4	150	30	5109035	¤
102.0	0.8	106.3	0.4	160	30	5109040	ι
127.0	0.8	131.8	0.4	230	30	5109045	ι
152.4	0.9	158.0	0.3	280	20	5109050	¤

Tolerance on length: ±1% (ISO 1307 Standard).

¤ Upon availability.