

SUPERMINES



GENERAL INDUSTRY



Air and water

APPLICATIONS

Extra heavy duty compressor hose for building sites, civil engineering projects, quarries, etc.

ADVANTAGES

- † Highly resistance to fatigue, bending and twisting.
- † Excellent resistance to abrasion, atmospheric conditions and dragging over rough and oily surfaces.
- † Good cold flexibility.
- † Suitable for oxygen discharge (ID≤25mm only).
- † Visible cover (yellow in colour).

TECHNICAL DESCRIPTION

Inner tube: SBR, black, smooth.

Reinforcement: synthetic textile.

Cover: SBR, yellow, smooth for ID≤25mm and fabric impression for ID>25mm.

Temperature range: -30°C to +70°C.

Electrical properties: non-conductive tube and cover.

7-25mm



35-50mm





GENERAL INDUSTRY

SUPERMINES



ID mm	WALL THICKNESS mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK () or min. order m
7.0 ±0.50	3.5	14.0 ±0.6	20	80	24.5	0.17	20	0072917	940
7.0 ±0.50	3.5	14.0 ±0.6	20	80	24.5	0.17	40	0072918	920
7.0 ±0.50	3.5	14.0 ±0.6	20	80	24.5	0.17	80	0072919	880
10.0 ±0.50	4.75	19.5 ±0.6	20	80	35.0	0.33	20	0072923	920
10.0 ±0.50	4.75	19.5 ±0.6	20	80	35.0	0.33	40	0072924	920
10.0 ±0.50	4.75	19.5 ±0.6	20	80	35.0	0.33	80	0072925	∞
13.4 ±0.60	4.85	23.1 ±0.7	20	60	48.0	0.41	20	0072929	∞
13.4 ±0.60	4.85	23.1 ±0.7	20	60	48.0	0.41	40	0072928	∞
13.4 ±0.60	4.85	23.1 ±0.7	20	60	48.0	0.41	80	0072927	1840
16.4 ±0.70	5.85	28.1 ±0.7	20	60	65.0	0.61	20	0072939	1480
16.4 ±0.70	5.85	28.1 ±0.7	20	60	65.0	0.61	40	0072938	1480
16.4 ±0.70	5.85	28.1 ±0.7	20	60	65.0	0.61	80	0072937	1440
19.4 ±0.70	5.85	31.1 ±0.8	20	60	77.0	0.69	20	0072949	∞
19.4 ±0.70	5.85	31.1 ±0.8	20	60	77.0	0.69	40	0072948	∞
19.4 ±0.70	5.85	31.1 ±0.8	20	60	77.0	0.69	80	0072947	∞
25.0 ±1.00	7	39.0 ±1.1	20	60	102.0	1.03	20	0072969	∞
25.0 ±1.00	7	39.0 ±1.1	20	60	102.0	1.03	40	0072968	∞
25.0 ±1.00	7	39.0 ±1.1	20	60	102.0	1.03	80	0072967	1520
35.0 ±1.00	8	51.0 ±2.0	20	80	250.0	1.57	20	0072979	200
35.0 ±1.00	8	51.0 ±2.0	20	80	250.0	1.57	40	0072983	200
50.0 ±1.25	9	68.0 ±2.5	20	80	350.0	2.44	20	0072991	200
50.0 ±1.25	9	68.0 ±2.5	20	80	350.0	2.44	40	0072994	200

Tolerance on length: ±1% (ISO 1307 Standard).

∞ Upon availability.

Digital version



TRELLEBORG

WWW.TRELLEBORG.COM/FLUIDHANDLING