

SUPERMINES



GENERAL INDUSTRY



Air and water

APPLICATIONS

Extra heavy duty compressor hose for building sites, civil engineering projects, quarries, etc.

AVANTAGES

- ┆ Highly resistance to fatigue, bending and twisting.
- ┆ Excellent resistance to abrasion, atmospheric conditions and dragging over rough and oily surfaces.
- ┆ Good cold flexibility.
- ┆ Suitable for oxygen discharge (ID≤25mm only).
- ┆ Visible cover (yellow in colour).

TECHNICAL DESCRIPTION

Inner tube SBR, color, smooth.

Reinforcement synthetic textile.

Cover SBR, color, smooth for ID≤25mm and fabric impression for ID>25mm.

Temperature range -30°C to +70°C.

Electrical properties non-conductive tube and cover.

7-25mm



35-50mm





GENERAL INDUSTRY

SUPERMINES



ID mm	WALL THICKNESS mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK () or min. order m
7.0 ±0.50	3.5	14.0 ±0.6	20	80	24.5	0.17	20	0072917	1
7.0 ±0.50	3.5	14.0 ±0.6	20	80	24.5	0.17	40	0072918	1480
7.0 ±0.50	3.5	14.0 ±0.6	20	80	24.5	0.17	80	0072919	1440
10.0 ±0.50	4.75	19.5 ±0.6	20	80	35.0	0.33	20	0072923	1
10.0 ±0.50	4.75	19.5 ±0.6	20	80	35.0	0.33	40	0072924	1
10.0 ±0.50	4.75	19.5 ±0.6	20	80	35.0	0.33	80	0072925	1520
13.4 ±0.60	4.85	23.1 ±0.7	20	60	48.0	0.41	20	0072929	1
13.4 ±0.60	4.85	23.1 ±0.7	20	60	48.0	0.41	40	0072928	1
13.4 ±0.60	4.85	23.1 ±0.7	20	60	48.0	0.41	80	0072927	2560
16.4 ±0.70	5.85	28.1 ±0.7	20	60	65.0	0.61	20	0072939	1
16.4 ±0.70	5.85	28.1 ±0.7	20	60	65.0	0.61	40	0072938	1560
16.4 ±0.70	5.85	28.1 ±0.7	20	60	65.0	0.61	80	0072937	1520
19.4 ±0.70	5.85	31.1 ±0.8	20	60	77.0	0.69	20	0072949	1
19.4 ±0.70	5.85	31.1 ±0.8	20	60	77.0	0.69	40	0072948	1
19.4 ±0.70	5.85	31.1 ±0.8	20	60	77.0	0.69	80	0072947	1
25.0 ±1.00	7	39.0 ±1.1	20	60	102.0	1.03	20	0072969	1
25.0 ±1.00	7	39.0 ±1.1	20	60	102.0	1.03	40	0072968	1
25.0 ±1.00	7	39.0 ±1.1	20	60	102.0	1.03	80	0072967	1520
35.0 ±1.00	8	51.0 ±2.0	20	80	250.0	1.57	20	0072979	200
35.0 ±1.00	8	51.0 ±2.0	20	80	250.0	1.57	40	0072983	200
50.0 ±1.25	9	68.0 ±2.5	20	80	350.0	2.44	20	0072991	200
50.0 ±1.25	9	68.0 ±2.5	20	80	350.0	2.44	40	0072994	200

Tolerance.

Digital version



TRELLEBORG

WWW.TRELLEBORG.COM/FLUIDHANDLING