

# AIRFLAT



## GENERAL INDUSTRY

Air and water



### APPLICATIONS

Light lay flat hose for public works, agriculture and all kinds of industries for multipurpose applications.

Designed for pumping and transport of water and similar liquids as well as compressed air, especially when long length and light weight are required and when sites are not easily accessible.

### ADVANTAGES

- † Easy to handle and store, very low weight, can be rolled flat.
- † High tensile resistance and excellent adhesion between rubber and textile.
- † Available in length up to 200m.
- † Oil and chemical resistant.
- † Good flexibility under pressure.
- † The hose withstands very rough handling but if it should be damaged just pull a hose sleeve of the same diameter over the damaged part of the hose (the expansion due to the pressure will seal the leak).

### TECHNICAL DESCRIPTION

Inner tube: oil resistant NBR, black, smooth.

Reinforcement: synthetic textile, woven.

Cover: ozone and oil resistant NBR, black, longitudinal fluted.

Temperature range: -20°C to +80°C.

Electrical properties: non conductive.


### COUPLINGS/FITTINGS

Claw couplings, with two double bolt clamps per fitting. Whip check safety cable is recommended especially for compressed air applications.

For dimensions above 25mm special couplings are recommended.

### COMPLEMENTARY INFORMATION

For compressed air applications, the use of hoses with ID exceeding 65mm is not recommended.





GENERAL INDUSTRY

AIRFLAT



ID mm	WALL THICKNESS mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK ( ) or min. order m
19.0	2.5	24.0	20	60	0.15	40	5503243	400
25.0	3.5	32.0	20	60	0.21	40	5503244	720
38.0	3.5	45.0	20	60	0.44	40	5503245	400
51.0	3.5	58.0	20	60	0.65	40	5503246	400
76.0	4	84.0	15	45	0.95	40	5503247	40
152.0	4	160.0	15	45	2.1	40	5503248	40

Tolerance on length:  $\pm 1\%$  (ISO 1307 Standard).

Digital version



TRELLEBORG

[WWW.TRELLEBORG.COM/FLUIDHANDLING](http://WWW.TRELLEBORG.COM/FLUIDHANDLING)