

# DIN 1TE



## GENERAL INDUSTRY

Hydraulic hoses



### APPLICATIONS

Textile reinforced rubber hose for hydraulic control lines.  
Discharge under pressure of hydraulic fluids, grease, oil-lubricated air and water.

### AVANTAGES

- † Light weight and flexible due to the textile reinforcement.
- † Elimination of vibrations in hydraulic lines.
- † Hose cover is highly resistant to oil and grease.

### TECHNICAL DESCRIPTION

Inner tube oil resistant NBR, color, smooth.

Reinforcement one textile spinned.

Cover oil and weather resistant CR, color, smooth.

Temperature range  
Hydraulic fluids: -40 °C to +100 °C.  
Aqueous liquids: -40 °C to +70 °C.  
Water: 0 °C to +70 °C.

### STANDARD/APPROVAL


EN 854 1TE:2015.



### COMPLEMENTARY INFORMATION

ID>16mm are not included in EN 854 1TE:2015.

Delivery terms for every order:  
50% in fixed length ;  
50% in random lengths:  
10-39m for all DN,  
41-99m for DN 4.8,  
41-119m for DN 6.4 to 15.9,  
41-79m for DN 19 to 25.4.



**GENERAL INDUSTRY****DIN 1TE**

ID inch	ID mm	WALL THICKNESS mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK ( ) or min. order m
3/16"	4.8	3 ±0.3	10.8	25	100	35	0.09	40	5501642	3520
3/16"	4.8	3 ±0.3	10.8	25	100	35	0.09	80	5501643	3520
3/16"	4.8	3 ±0.3	10.8	25	100	35	0.09	100	5501644	3500
1/4"	6.4	3 ±0.3	12.4	25	100	45	0.11	40	5501647	∅
1/4"	6.4	3 ±0.3	12.4	25	100	45	0.11	80	5501648	3520
1/4"	6.4	3 ±0.3	12.4	25	100	45	0.11	120	5501649	∅
5/16"	7.9	3 ±0.3	13.9	20	80	65	0.13	40	5501652	∅
5/16"	7.9	3 ±0.3	13.9	20	80	65	0.13	80	5501653	∅
5/16"	7.9	3 ±0.3	13.9	20	80	65	0.13	120	5501654	∅
3/8"	9.5	3 ±0.3	15.5	20	80	75	0.15	40	5501657	∅
3/8"	9.5	3 ±0.3	15.5	20	80	75	0.15	80	5501658	∅
3/8"	9.5	3 ±0.3	15.5	20	80	75	0.15	120	5501659	∅
1/2"	12.7	3 ±0.3	18.7	16	64	90	0.18	40	5501662	∅
1/2"	12.7	3 ±0.3	18.7	16	64	90	0.18	80	5501663	2480
1/2"	12.7	3 ±0.3	18.7	16	64	90	0.18	120	5501664	∅
5/8"	15.9	3.5 ±0.4	22.9	16	64	115	0.26	40	5501667	1200
5/8"	15.9	3.5 ±0.4	22.9	16	64	115	0.26	80	5501668	1200
5/8"	15.9	3.5 ±0.4	22.9	16	64	115	0.26	120	5501669	1200
3/4"	19.0	3.5 ±0.4	26.0	12	32	135	0.3	40	5501672	1120
3/4"	19.0	3.5 ±0.4	26.0	12	32	135	0.3	80	5501673	1120
1"	25.4	4 ±0.4	33.4	12	32	165	0.45	40	5501674	760
1"	25.4	4 ±0.4	33.4	12	32	165	0.45	80	5501675	720

Tolerance.

