

TRELLOIL D EC



OIL & GAS

Oil and petroleum
Oil cargo



APPLICATIONS

Transfer of petroleum products with aromatic content up to 50% in large diameters.

ADVANTAGES

- † Highly robust and flexible.
- † Cover particularly resistant to hydrocarbons, abrasion, atmospheric conditions and ozone.
- † Electrical conductivity fully assured by the inner tube compound.

TECHNICAL DESCRIPTION

Inner tube: oil and petrol resistant NBR, black, smooth.

Reinforcement: synthetic textile.

Cover: oil and weather resistant CR, black, fabric impression.

Temperature range: -40 °C to +100 °C.

Electrical properties: conductive tube, $R < 10^6 \Omega / \text{lg}$.

COMPLEMENTARY INFORMATION


Can be delivered with swaged fittings: steel flange PN20 or larger, Victaulic, male or female threaded fittings.
Please consult us for any other type of ends or delivery lengths.

TRELLOIL D EC WP 20 BAR



TRELLEBORG

TRELLOIL D EC WP 20 BAR





OIL & GAS

TRELLOIL D EC



ID mm	WALL THICKNESS mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK () or min. order m
100.0 ±1.5	9 ±0.8	118.0 ±1.5	20	60	600	4.08	1	5513112	40
125.0 ±1.5	9 ±0.8	143.0 ±1.5	20	60	750	5.04	1	5513113	40
150.0 ±1.5	10 ±0.8	170.0 ±1.5	20	60	900	6.5	1	5513114	40
204.0 ±1.5	11 ±1.0	226.0 ±1.5	20	60	1400	9.81	1	5513115	40

Tolerance on length: ±1% (ISO 1307 Standard).

Digital version



TRELLEBORG

WWW.TRELLEBORG.COM/FLUIDHANDLING