

E569

EPDM



EPDM SHEETING WHITE FOOD QUALITY

FEATURES

EPDM, white, food grade, meeting regulation (EC) 1935/2004 (European legislation) and FDA classification (American legislation).

REGULATIONS

- Meeting european regulations (EC) n.1935/2004 and 2023/2006.
- The material is in compliance with FDA 21 CFR Part. 177. Indirect Food Additives: Polymers. Sec 177.2600 Rubber articles intended for repeated use for contact with aqueous food.
- IANESCO certificate (Institut français de Poitiers).
- Quality certificate available under request.

APPLICATIONS

Gaskets or washers cutting and manufacturing of pieces for general industrial purpose applications in contact with:

- foodstuffs
- water (maximum temperature +100 °C)
- oxidizing and non oxidizing diluted acids

Non suitable for contact with oil or vegetable fats.

ADVANTAGES

- Very good resistance to ozone and ageing
- Excellent temperature resistance (-40/+115 °C)
- Good ratio quality/price
- Matte finish to guarantee a good surface finished quality and to secure an easy unrolling.

BENEFITS

- Performance
- Legality
- Hygiene, cleanliness
- Food safety

MAINTENANCE RECOMMENDATION

Always follow manufacturer warnings and instructions when using any cleaning product.

MECHANICAL, PHYSICAL AND CHEMICAL PROPERTIES

Measured characteristics		Standard	Value	
MECHANICAL				
Rubber compound - white			EPDM	
Density			1.27 ±0.05	g/cm ³
Hardness	ASTM D2240		60 ±5	Shore A
Tensile strength	ISO 37		≥8	MPa
Elongation at break	ISO 37		≥350	%
Tear resistance	ISO 34-1		≥18	N/mm
Compression set after 22h at 70 °C	ISO 815-1		≤40	%
TEMPERATURE				
Working temperature			-40/+115	°C
AGEING				
Δ Hardness after 70h at 70 °C		ASTM D573	≤5	Shore A
Δ Tensile strength after 70h at 70 °C		ASTM D573	≤15	%
Δ Elongation at break after 70h at 70 °C		ASTM D573	≤40	%
Ozone resistance, 200pphm, 48h, 38 °C, 20%		ASTM D1149 type A	No crack	

CHEMICAL RESISTANCE

Diluted acids and bases	Concentrated acids and bases	Ozone	Oils and hydrocarbons
Very good	Good	Very good	Non suitable

IDENTIFICATION

Branding	Without.
Packaging	Thickness ≤6mm rolled on cardboard tube Ø 80mm. Thickness >6mm in roll.
Wrapping	White polyethylene film.
Labelling	Self-adhesive label indicating product name, dimensions, area in m ² , nominal weight, and product code to allow product traceability.

Unless typographical error, information and figures of our technical datasheet are based on our experience and laboratory tests according to international standards. This data is intended to be used as a guideline only. Material performance depends on the conditions of use and the final application.

EPDM		EPDM SHEETING		E569	
THICKNESS mm	WIDTH mm	LENGTH m	WEIGHT kg/m ²	SIDES FINISH	
1±0.2	1400±2%	20±2%	1.26	2 SIDES MATT	
1.5±0.25	1400±2%	15±2%	1.9	2 SIDES MATT	
2±0.3	1400±2%	15±2%	2.53	2 SIDES MATT	
3±0.3	1400±2%	10±2%	3.79	2 SIDES MATT	
4±0.4	1400±2%	10±2%	5.06	2 SIDES MATT	
5±0.4	1400±2%	10±2%	6.32	2 SIDES MATT	
6±0.5	1400±2%	10±2%	7.59	1 SIDE SMOOTH/1 SIDE MATT	
8±0.7	1400±2%	5±2%	10.03	1 SIDE SMOOTH/1 SIDE MATT	
10±1.0	1400±2%	5±2%	12.53	1 SIDE SMOOTH/1 SIDE MATT	

