

PUSH-LOCK BLACK



GENERAL INDUSTRY

Auto process



APPLICATIONS

Ideally designed for hydraulic pneumatic low pressure lines for robotic in automotive industries.

Used with push-on fittings at maximum working pressure of 16bar (250psi).

Not suitable for impulse pressure application.

ADVANTAGES

- ┆ 40, 80 and 100m delivered in one piece on wooden reel.
- ┆ Very good abrasion resistance.
- ┆ Flexibility, light weight and easy handling.
- ┆ Free from silicone.

TECHNICAL DESCRIPTION

Inner tube: oil resistant NBR/PVC, black, smooth.

Reinforcement: one textile braid.

Cover: abrasion, oil and weather resistant NBR/PVC, black, smooth.

Temperature range:

Air: -20 °C/+110 °C (peak +125 °C).

Water: 0 °C/+100 °C (peak +110 °C).

Hydraulic oils: -20 °C/+70 °C (peak +90 °C).

Water glycol: -20 °C/+70 °C (peak +90 °C).

Electrical properties: non-conductive inner tube, $R > 10^{12} \Omega/m$.

COUPLINGS/FITTINGS

Used with push-on fittings at maximum working pressure of 16bar (250psi).

COMPLEMENTARY INFORMATION

40, 80 and 100m: delivered in one piece on wooden reel.

20m: delivered in coils with PE film on palet.

**GENERAL INDUSTRY****PUSH-LOCK BLACK**

ID inch	ID mm	OD mm	WORKING PRESSURE bar psi	BURSTING PRESSURE bar psi	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK () or min. order m
1/4	6.3 ±0.4	12.4 ±0.8	16 250.0	64 1000.0	45	0.11	20	5503501	☒
1/4	6.3 ±0.4	12.4 ±0.8	16 250.0	64 1000.0	45	0.11	40	5503502	☒
1/4	6.3 ±0.4	12.4 ±0.8	16 250.0	64 1000.0	45	0.11	100	5503503	☐
3/8	9.6 ±0.5	15.5 ±0.8	16 250.0	64 1000.0	75	0.16	20	5503504	☒
3/8	9.6 ±0.5	15.5 ±0.8	16 250.0	64 1000.0	75	0.16	40	5503505	☒
3/8	9.6 ±0.5	15.5 ±0.8	16 250.0	64 1000.0	75	0.16	100	5503506	☐
1/2	12.7 ±0.6	18.7 ±1.0	16 250.0	64 1000.0	90	0.19	20	5503507	☒
1/2	12.7 ±0.6	18.7 ±1.0	16 250.0	64 1000.0	90	0.19	40	5503508	☒
1/2	12.7 ±0.6	18.7 ±1.0	16 250.0	64 1000.0	90	0.19	100	5503509	☐
5/8	16.0 ±0.6	22.9 ±1.0	16 250.0	64 1000.0	115	0.28	20	5503510	☒
5/8	16.0 ±0.6	22.9 ±1.0	16 250.0	64 1000.0	115	0.28	40	5503511	☒
5/8	16.0 ±0.6	22.9 ±1.0	16 250.0	64 1000.0	115	0.28	80	5503512	☒
3/4	19.2 ±0.6	26.5 ±1.0	16 250.0	64 1000.0	135	0.34	20	5503513	☒
3/4	19.2 ±0.6	26.5 ±1.0	16 250.0	64 1000.0	135	0.34	40	5503514	☒
3/4	19.2 ±0.6	26.5 ±1.0	16 250.0	64 1000.0	135	0.34	80	5503515	☐

Tolerance on length: ±1% (ISO 1307 Standard).

☐ Upon availability.

Digital version

**TRELLEBORG**WWW.TRELLEBORG.COM/FLUIDHANDLING