

REDFINE NR



MEDIUM WEAR SHEETING FINE GRAIN SIZE MATERIAL

FEATURES

Wear resistant natural rubber, red.

APPLICATIONS

Hoppers, chutes, operating cyclones, vibrating lines, silos, etc., linings to protect equipment against very abrasive fine grain size products wear, due to their very nature (rock, wood, metal, all fine particle size materials, chemical products, etc.), density and hardness (medium to high), forms (fine particles, bulks, etc.), with dry conditions and maximum temperature +70 °C.

Manufacturing of rubber skirts.

Hanging panels fostering materials cleaning and removal.

Areas of activity: sand and gravel quarries, aggregate and cement industries, concrete plants, etc.

ADVANTAGES

- † Excellent mechanical properties: tensile strength, elongation at break, tear resistance, abrasion, etc.
- † Excellent resistance to fine grain size products projection and fretting wear: sand, shot blasting, fine particles, abrasive dust, etc.
- † Corrosion protection
- † Noise and vibration propagation reduction
- † Possibility to be produced with bonding layer for cold vulcanizing or with steel backing for mechanical fixing

BENEFITS

- † Performance
- † Safety
- † Reliability
- † Service life


MECHANICAL, PHYSICAL AND CHEMICAL PROPERTIES

Measured characteristics		Standard	Value	
MECHANICAL				
Rubber compound - red			NR	R492
Density			1.05 ±0.05	g/cm ³
Hardness	ASTM D2240		45 ±5	Shore A
Tensile strength	ISO 37		≥16	MPa
Elongation at break	ISO 37		≥600	%
Tear resistance	ISO 34-1		≥25	N/mm
Abrasion resistance (5N)	ISO 4649		≤80	mm ³
Compression set after 24h at 70 °C	ISO 815-1		≤30	%
TEMPERATURE				
Working temperature			-40/+85	°C
AGEING				
Δ Hardness after 70h at 70 °C	ASTM D573		≤5	Shore A
Δ Tensile strength after 70h at 70 °C	ASTM D573		≤-15	%
Δ Elongation at break after 70h at 70 °C	ASTM D573		≤-25	%
CHEMICAL RESISTANCE				
Diluted acids and bases	Concentrated acids and bases	Ozone	Oils and hydrocarbons	
Very good	Good	Medium	Non suitable	

IDENTIFICATION

Branding	Without.
Packaging	Thickness ≤6mm rolled on cardboard tube Ø 80mm. Thickness >6mm in roll. Bonding layer internal side protected by a white polypropylene film, easily removable by hand.
Wrapping	Black polyethylene film.
Labelling	Self-adhesive label indicating product name, dimensions, area in m ² , nominal weight, and product code to allow product traceability.

Unless typographical error, information and figures of our technical datasheet are based on our experience and laboratory tests according to international standards. This data is intended to be used as a guideline only. Material performance depends on the conditions of use and the final application.

NR	MEDIUM WEAR SHEETING	REDFINE						
			THICKNESS mm	WIDTH mm	LENGTH m	WEIGHT kg/m ²	SIDES FINISH	OPTION (BL = bonding layer)
			3±0.3	1400±2%	10±2%	3.15	2 SMOOTH SIDES	
			4±0.4	1400±2%	10±2%	4.16	2 SMOOTH SIDES	
			5±0.4	1400±2%	10±2%	5.2	2 SMOOTH SIDES	
			6±0.5	1400±2%	10±2%	6.25	2 SMOOTH SIDES	
			6±0.5	1400±2%	10±2%	7.52	1 SIDE SMOOTH/1 SIDE BONDING LAYER	BL
			8±0.7	1400±2%	10±2%	8.3	2 SMOOTH SIDES	
			8±0.7	1400±2%	10±2%	8.95	1 SIDE SMOOTH/1 SIDE BONDING LAYER	BL
			10±1.0	1400±2%	10±2%	10.41	2 SMOOTH SIDES	
			10±1.0	1400±2%	10±2%	11.03	1 SIDE SMOOTH/1 SIDE BONDING LAYER	BL
			12±1.0	1400±2%	5±2%	12.49	2 SMOOTH SIDES	
			12±1.0	1400±2%	5±2%	12.62	1 SIDE SMOOTH/1 SIDE BONDING LAYER	BL
			15±1.0	1400±2%	5±2%	15.61	2 SMOOTH SIDES	
			15±1.0	1400±2%	5±2%	16	1 SIDE SMOOTH/1 SIDE BONDING LAYER	BL
			20±1.4	1400±2%	5±2%	20.8	2 SMOOTH SIDES	

