




CIRCULAR CIRCULAR STUDS



STANDARD MATTING

FEATURES

Non-slip surface.
Circular studs.
Thermal and acoustic insulation.

APPLICATIONS

Basic flooring for industrial use.

WARNING: for public areas where more demanding safety is required, we advise the use of our fire resistant and low and non toxic smoke emission qualities.

ADVANTAGES

- ┆ Prevents the risk of persons falling
- ┆ Visibility
- ┆ Easy to clean and low maintenance
- ┆ Noise, vibration, and cold propagation reduction


BENEFITS

- ┆ Safety
- ┆ Cleanliness, hygiene
- ┆ Comfort
- ┆ Economy

MECHANICAL, PHYSICAL AND CHEMICAL PROPERTIES

	Measured characteristics	Standard	Value	
MECHANICAL	Rubber compound		SBR	
	Hardness	ASTM D2240	70 ±5	Shore A
	Abrasion resistance (5N)	ISO 4649	≤250	mm ³

PROFILE




Circular studs (MC 2K1)

IDENTIFICATION

Branding	Without.
Back face	Fabric impression.
Packaging	Rolled on cardboard tube Ø 80mm.
Wrapping	Black polyethylene film.
Labelling	Self-adhesive label indicating product name, dimensions, area in m ² , nominal weight, and product code to allow product traceability.

Unless typographical error, information and figures of our technical datasheet are based on our experience and laboratory tests according to international standards. This data is intended to be used as a guideline only. Material performance depends on the conditions of use and the final application.

CIRCULAR STUDS	STANDARD MATTING	CIRCULAR			
COLOR	THICKNESS mm	WIDTH mm	LENGTH m	WEIGHT kg/m ²	PATTERN
BLACK	3 ± 0.3	1000 ± 2 %	10 ± 2 %	4.06	MC 2K1
BLACK	3 ± 0.3	1200 ± 2 %	10 ± 2 %	4.06	MC 2K1

Depending on the manufacturing process there could be differences in some tonalities of the roll colours.
Colours of the sample kits and catalogues has to be considered as indicative.

