




GROOVED + GROOVED MATTING



TECHNICAL MATTING / HIGH PERFORMANCE

FEATURES

Grooved profile.

APPLICATIONS

Floor mats, protection of walls, partitions, doors, columns, for public places and production units.

Elevators mats, production units lifts.

Entrance mats for supermarkets or chain stores.

Mats for vans, cars, trucks.

Acoustic insulating partitions.

Decoration panels.

Indoor installations.

ADVANTAGES

- High dimensional and color stability
- High hardness and abrasion properties, which means a better transit resistance
- Good scratch resistance
- Good adhesion to different possible substrates
- Very good wear and tear resistance
- Non-slippery
- Acoustic insulation
- Low maintenance thanks to grooved profile enabling easy water and washing products removal
- Excellent walking and standing comfort

BENEFITS

- Cleanliness, hygiene
- Comfort
- Safety


MECHANICAL, PHYSICAL AND CHEMICAL PROPERTIES

Measured characteristics	Standard	Value	
MECHANICAL			
Rubber compound		SBR NR	
Hardness	ASTM D2240	70 ±5	Shore A
Abrasion resistance (5N)	ISO 4649	≤200	mm ³
Residual indentation	EN ISO 24343	≤0.15	mm
Dimensional stability	EN ISO 23999	±0.3	%
Sound insulation	ISO 10140-3	12	dB


CHEMICAL RESISTANCE

Common cleaning products	EN 423	Good
--------------------------	--------	------

PROFILE



PATTERN




Wide ribbed M39 (MG)

IDENTIFICATION

Branding	Without.
Back face	Fabric impression.
Packaging	Rolled on cardboard tube Ø 80mm.
Wrapping	Black polyethylene film.
Labelling	Self-adhesive label indicating product name, dimensions, area in m ² , nominal weight, and product code to allow product traceability.

Unless typographical error, information and figures of our technical datasheet are based on our experience and laboratory tests according to international standards. This data is intended to be used as a guideline only. Material performance depends on the conditions of use and the final application.

GROOVED MATTING	TECHNICAL MATTING / HIGH PERFORMANCE	GROOVED +			
			COLOR	THICKNESS mm	WIDTH mm
BLACK	5 ±0.4	1400 ± 2 %	10 ± 2 %	5.81	MG
Other colours are available under request					

