

GROOVED + GROOVED MATTING



TECHNICAL MATTING / HIGH PERFORMANCE

Caractéristiques

Grooved profile.

Applications

Floor mats, protection of walls, partitions, doors, columns, for public places and production units.

Elevators mats, production units lifts.

Entrance mats for supermarkets or chain stores.

Mats for vans, cars, trucks.

Acoustic insulating partitions.

Decoration panels.

Indoor installations.

Advantages

- ▮ High dimensional and color stability
- ▮ High hardness and abrasion properties, which means a better transit resistance
- ▮ Good scratch resistance
- ▮ Good adhesion to different possible substrates
- ▮ Very good wear and tear resistance
- ▮ Non-slippery
- ▮ Acoustic insulation
- ▮ Low maintenance thanks to grooved profile enabling easy water and washing products removal
- ▮ Excellent walking and standing comfort

Bénéfices

- ▮ Cleanliness, hygiene
- ▮ Comfort
- ▮ Safety


PROPRIETES MECANIQUES ET PHYSICO CHIMIQUES

Caractéristiques mesurées	Norme de référence	Valeur	
MECANIQUES			
Elastomère		SBR NR	
Dureté	ASTM D2240	70 ±5	Shore A
Résistance à l'abrasion (5N)	ISO 4649	≤200	mm ³
Empreinte résiduelle	EN ISO 24343	≤0.15	mm
Stabilité dimensionnelle	EN ISO 23999	±0.3	%
Isolation acoustique	ISO 10140-3	12	dB

Résistance Chimique

,Produits de nettoyage courants	EN 423	Good
---------------------------------	--------	------

Profil



Aspect




Wide ribbed M39 (MG)

Identification

Marquage	Without.
Face arrière	Fabric impression.
Conditionnement	Rolled on cardboard tube Ø 80mm.
Emballage	Black polyethylene film.
Étiquetage	Self-adhesive label indicating product name, dimensions, area in m ² , nominal weight, and product code to allow product traceability.

Identification

GROOVED MATTING	TECHNICAL MATTING / HIGH PERFORMANCE	GROOVED +			
COLOR	EPAISSEUR mm	LARGEUR mm	LONGEUR m	WEIGHT kg/m ²	ASPECT
FF094	5 ±0.4	1400 ± 2 %	10 ± 2 %	5.81	MG
Other colours are available under request					

