

PULSOR 170 L-WHIP



CONSTRUCTION & INFRASTRUCTURE

Concrete pump and placement



APPLICATIONS

High pressure concrete pump hose for boom transfer, placement.

ADVANTAGES

- ┆ Prevents whipping effects when air is compressed in the delivery system, then released.
- ┆ Avoids risks of injuries.
- ┆ Highly abrasion resistant hose to give extended service life.

TECHNICAL DESCRIPTION

Inner tube: abrasion resistant NR/SBR, black, smooth.

Reinforcement: 4 steel cords plies and specific reinforcement.

Cover: abrasion and weather resistant NR/SBR, black, fabric impression.

Temperature range: -30°C to +80°C.

COUPLINGS/FITTINGS

Hose assembly delivered with one crimped coupling according to VICTAULIC or concrete pump manufacturers (PUTZMEISTER, SCHWING, etc.) dimensions.

COMPLEMENTARY INFORMATION

Regular safety rule should be observed and the area around hose end should be evacuated during cleaning operation whenever pumping deviation occurs indicating air in the boom.

OR 170 L-WHIP



Made in France



TRELLEBORG

PULSOR 170 L-WHIP



**CONSTRUCTION &
INFRASTRUCTURE****PULSOR 170 L-WHIP**

ID mm	WALL THICKNESS mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	MAX. VACUUM bar	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK () or min. order m
102.0	13 ±1.0	129.0 ±2.0	85	170	0.8	7.93	1	5603103	1
125.0	14 ±1.0	154.0 ±2.0	85	170	0.8	10.25	1	5603247	1

Tolerance on length: ±1% (ISO 1307 Standard).

**TRELLEBORG**

WWW.TRELLEBORG.COM/FLUIDHANDLING