




# CHECKER CHECKER MATTING



## STANDARD MATTING

### FEATURES

Checkered pattern.

### APPLICATIONS

Basic flooring for industrial use.

### ADVANTAGES

- Non-slippery
- Thermal and acoustic insulation
- Noise, vibration, and cold propagation reduction
- Very good wear and tear resistance
- Excellent walking and standing comfort
- Easy to clean and low maintenance

### BENEFITS

- Safety
- Comfort
- Economy

## MECHANICAL, PHYSICAL AND CHEMICAL PROPERTIES

Measured characteristics	Standard	Value	
MECHANICAL			
Rubber compound		SBR	
Hardness	ASTM D2240	70 ±5	Shore A
Abrasion resistance (5N)	ISO 4649	≤250	mm <sup>3</sup>

## PROFILE


## PATTERN



Checker (MK)

IDENTIFICATION	
Branding	Without.
Back face	Fabric impression.
Packaging	Rolled on cardboard tube Ø 80mm.
Wrapping	Black polyethylene film.
Labelling	Self-adhesive label indicating product name, dimensions, area in m <sup>2</sup> , nominal weight, and product code to allow product traceability.

Unless typographical error, information and figures of our technical datasheet are based on our experience and laboratory tests according to international standards. This data is intended to be used as a guideline only. Material performance depends on the conditions of use and the final application.

CHECKER MATTING	STANDARD MATTING	CHECKER			
COLOR	THICKNESS mm	WIDTH mm	LENGTH m	WEIGHT kg/m <sup>2</sup>	PATTERN
BLACK	3 ± 0.3	1400 ± 2 %	10 ± 2 %	3.9	MK

