

CANALKLER 250 S ASSEMBLY



**CONSTRUCTION &
INFRASTRUCTURE**

Drain and sewer cleaning



APPLICATIONS

Sewer jetting and heavy duty, high pressure water cleaning.

ADVANTAGES

- | Very low sliding resistance which allows: higher cleaning efficiency, reduction of cleaning time and therefore, reduction of fuel consumption.
- | Longer lifespan thanks to the special cover compound with higher abrasion resistance.
- | Better flexibility, even at low temperatures.
- | Easy to handle and user friendly.
- | Deformation resistance.
- | Extra high strength and security due to aramide reinforcement.

TECHNICAL DESCRIPTION

Inner tube: SBR, black, smooth.

Reinforcement: aramide textile, braided.

Cover: SBR/NR, black, smooth. Very low sliding resistance.

Temperature range: -30 °C to +80 °C.

COUPLINGS/FITTINGS


All hoses are assembled with BSP female/BSP male.

All assembled hoses are pressure tested at 375bar and have an unique hose number.

COMPLEMENTARY INFORMATION

Delivered with test certificate on each factory assembled hose.

Embossed branding



TRELLEBORG

CANALKLER 250 S SEWER CLEANING HOSE WP 250 BAR/3600 PSI quarter/year Made in France



ID mm	WALL THICKNESS mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK () or min. order m
13.0 ±0.5	6.3 ±0.5	25.6	250	625	70	0.45	40	5014178	⌈
13.0 ±0.5	6.3 ±0.5	25.6	250	625	70	0.45	60	5014179	⌈
13.0 ±0.5	6.3 ±0.5	25.6	250	625	70	0.45	80	5014180	⌈
13.0 ±0.5	6.3 ±0.5	25.6	250	625	70	0.45	100	5014916	⌈
13.0 ±0.5	6.3 ±0.5	25.6	250	625	70	0.45	120	5014005	⌈
19.0 ±0.6	6.3 ±0.5	31.6	250	625	90	0.61	40	5014181	⌈
19.0 ±0.6	6.3 ±0.5	31.6	250	625	90	0.61	80	5014182	⌈
19.0 ±0.6	6.3 ±0.5	31.6	250	625	90	0.61	100	5014459	⌈
19.0 ±0.6	6.3 ±0.5	31.6	250	625	90	0.61	120	5014006	⌈
25.0 ±0.8	7.15 ±0.5	39.3	250	625	100	0.9	40	5014183	⌈
25.0 ±0.8	7.15 ±0.5	39.3	250	625	100	0.9	50	5014874	⌈
25.0 ±0.8	7.15 ±0.5	39.3	250	625	100	0.9	80	5014184	⌈
25.0 ±0.8	7.15 ±0.5	39.3	250	625	100	0.9	100	5014238	⌈
25.0 ±0.8	7.15 ±0.5	39.3	250	625	100	0.9	120	5014007	⌈
25.0 ±0.8	7.15 ±0.5	39.3	250	625	100	0.9	150	5014461	⌈
25.0 ±0.8	7.15 ±0.5	39.3	250	625	100	0.9	160	5014185	⌈
25.0 ±0.8	7.15 ±0.5	39.3	250	625	100	0.9	180	5014186	⌈
25.0 ±0.8	7.15 ±0.5	39.3	250	625	100	0.9	200	5014520	⌈
25.0 ±0.8	7.15 ±0.5	39.3	250	625	100	0.9	240	5014733	⌈
32.0 ±1.0	7.8 ±0.6	47.6	250	625	130	1.12	40	5014187	⌈
32.0 ±1.0	7.8 ±0.6	47.6	250	625	130	1.12	80	5014188	⌈
32.0 ±1.0	7.8 ±0.6	47.6	250	625	130	1.12	120	5014008	⌈
32.0 ±1.0	7.8 ±0.6	47.6	250	625	130	1.12	150	5014466	⌈
32.0 ±1.0	7.8 ±0.6	47.6	250	625	130	1.12	160	5014189	⌈
32.0 ±1.0	7.8 ±0.6	47.6	250	625	130	1.12	180	5014190	⌈
32.0 ±1.0	7.8 ±0.6	47.6	250	625	130	1.12	200	5014655	⌈
38.0 ±1.0	8 ±0.8	54.0	250	500	155	1.35	120	5014009	⌘

Tolerance on length: ±1% (ISO 1307 Standard).

⌘ Upon availability.

Digital version



TRELLEBORG

WWW.TRELLEBORG.COM/FLUIDHANDLING