

# KLENET



## FOOD & BEVERAGE

Food industry  
Cleaning



### APPLICATIONS

Washdown and cleaning in food processing industries, canneries, dairies, slaughterhouses, etc.

### ADVANTAGES

- † Very good resistance to high temperatures.
- † Smooth for easy handling with light-coloured, non-marking cover.
- † Excellent resistance of the cover compound to animal and vegetable grease.
- † Contains no phthalate.

### TECHNICAL DESCRIPTION

Inner tube: food grade quality oil resistant NBR, white, smooth.

Reinforcement: synthetic textile.

Cover: oil and weather resistant NBR/PVC, blue, smooth.

Temperature range: -20 °C to +95 °C.

### STANDARD/APPROVAL

EU regulations No. 1935/2004, 2023/2006.



FDA regulation No. 21 CFR 177.2600.



German legislation: BfR recommendation XXI cat. 3.



French legislation.



All relevant migrations tests (France and FDA) were performed by the French institute of Poitiers (IANESCO) and confirmed compliant.

### COUPLINGS/FITTINGS

Specially designed fittings are available, please contact us for further information in order to get optimum connections.

### COMPLEMENTARY INFORMATION


Not recommended with washdown guns.

and embossed: week/year - batch number

TRELLEBORG

KLENET -  - WP 10 BAR

95 °C - Made in France



**FOOD & BEVERAGE****KLENET**

| ID<br>mm  | OD<br>mm  | WORKING<br>PRESSURE<br>bar | BURSTING<br>PRESSURE<br>bar | BENDING<br>RADIUS<br>mm | WEIGHT<br>kg/m | LENGTH<br>m | ARTICLE<br>NUMBER | STOCK (1) or<br>min. order<br>m |
|-----------|-----------|----------------------------|-----------------------------|-------------------------|----------------|-------------|-------------------|---------------------------------|
| 13.0 ±0.5 | 21.4 ±0.7 | 10                         | 30                          | 80                      | 0.3            | 20          | 0060962           | 1                               |
| 13.0 ±0.5 | 21.4 ±0.7 | 10                         | 30                          | 80                      | 0.3            | 40          | 0060961           | 1                               |
| 13.0 ±0.5 | 21.4 ±0.7 | 10                         | 30                          | 80                      | 0.3            | 60          | 0060952           | 2                               |
| 13.0 ±0.5 | 21.4 ±0.7 | 10                         | 30                          | 80                      | 0.3            | 120         | 0060953           | 1                               |
| 16.0 ±0.7 | 25.0 ±0.8 | 10                         | 30                          | 95                      | 0.38           | 20          | 0060964           | 1                               |
| 16.0 ±0.7 | 25.0 ±0.8 | 10                         | 30                          | 95                      | 0.38           | 40          | 0060963           | 1                               |
| 16.0 ±0.7 | 25.0 ±0.8 | 10                         | 30                          | 95                      | 0.38           | 60          | 0060954           | 2                               |
| 16.0 ±0.7 | 25.0 ±0.8 | 10                         | 30                          | 95                      | 0.38           | 120         | 0060955           | 1                               |
| 19.0 ±0.7 | 28.4 ±0.8 | 10                         | 30                          | 115                     | 0.48           | 20          | 0060966           | 1                               |
| 19.0 ±0.7 | 28.4 ±0.8 | 10                         | 30                          | 115                     | 0.48           | 40          | 0060965           | 1                               |
| 19.0 ±0.7 | 28.4 ±0.8 | 10                         | 30                          | 115                     | 0.48           | 60          | 0060956           | 1                               |
| 25.0 ±1.0 | 35.0 ±1.1 | 10                         | 30                          | 155                     | 0.62           | 20          | 0060968           | 1                               |
| 25.0 ±1.0 | 35.0 ±1.1 | 10                         | 30                          | 155                     | 0.62           | 40          | 0060967           | 1                               |
| 25.0 ±1.0 | 35.0 ±1.1 | 10                         | 30                          | 155                     | 0.62           | 60          | 0060957           | 2                               |

Tolerance on length: ±1% (ISO 1307 Standard).

2 Upon availability.

Digital version

