


OILMAT NBR



TECHNICAL MATTING / OIL AND HYDROCARBON RESISTANT

FEATURES

Circular studs or checkered pattern.

APPLICATIONS

Suitable for industrial site.

Indoor installations.

Warehouses, aisles, locker rooms, machine or heavy equipment fronts, with fatty products projection.

ADVANTAGES

- † Good resistance to animal or vegetable oils and fats (maximum +50°C) and non-aromatic hydrocarbons
- † Conductor of electricity
- † Thermal and acoustic insulation
- † Excellent walking and standing comfort
- † Non-slippery
- † Easy to clean and low maintenance
- † Noise, vibration, and cold propagation reduction

BENEFITS

- † Safety
- † Cleanliness, hygiene
- † Comfort
- † Service life



MECHANICAL, PHYSICAL AND CHEMICAL PROPERTIES

Measured characteristics	Standard	Value	
MECHANICAL			
Rubber compound		NBR	
Hardness	ASTM D2240	70 ±5	Shore A
Abrasion resistance (5N)	ISO 4649	≤200	mm ³
Residual indentation	EN ISO 24343	≤0.15	mm
Dimensional stability	EN ISO 23999	±0.3	%
Sound insulation	ISO 10140-3	12	dB

CHEMICAL RESISTANCE

Common cleaning products	EN 423	Good
--------------------------	--------	------

PROFILE



PATTERN



Circular studs (MC 2K1)



Circular studs (MC 7A)




Checker (MK)

IDENTIFICATION

Branding	Without.
Back face	Circular studs MC 2K1: with fabric impression backing. Circular studs MC 7A: buffed. Checker: with fabric impression backing.
Packaging	Rolled on cardboard tube Ø 80mm.
Wrapping	Black polyethylene film.
Labelling	Self-adhesive label indicating product name, dimensions, area in m ² , nominal weight, and product code to allow product traceability.

Unless typographical error, information and figures of our technical datasheet are based on our experience and laboratory tests according to international standards. This data is intended to be used as a guideline only. Material performance depends on the conditions of use and the final application.

NBR	TECHNICAL MATTING / OIL AND HYDROCARBON RESISTANT	OILMAT			
COLOR	THICKNESS mm	WIDTH mm	LENGTH m	WEIGHT kg/m ²	PATTERN
BLACK	3 ± 0.3	1000 ± 2 %	10 ± 2 %	3.72	MC 2K1
BLACK	3 ± 0.3	1200 ± 2 %	10 ± 2 %	4.4	MC 2K1
BLACK	3 ± 0.3	1400 ± 2 %	10 ± 2 %	3.74	MK
BLACK	4.5 ± 0.4	1000 ± 2 %	10 ± 2 %	5.73	MC 7A

