

TRELLVAC Handler MD



MINING & QUARRIES

Evacuation and material handling
hoses



APPLICATIONS

Medium duty working hose on vacuum cleaning trucks for use at the work site.

ADVANTAGES

- Light and flexible with good wear resistance.
- Specially designed for light materials transport and very easy handling.

TECHNICAL DESCRIPTION

Inner tube: wear resistant NR, black, smooth.

Reinforcement: synthetic textile, woven fabric with embedded steel helix.

Cover: wear and weather resistant SBR, black, corrugated.

Temperature range: -30°C to +90°C.

Electrical properties: non conductive tube.

COMPLEMENTARY INFORMATION

OD measured on top of corrugation.



**MINING & QUARRIES****TRELLVAC Handler MD**

ID mm	OD mm	MAX. VACUUM bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK () or min. order m
51.0	63.0 ± 1.5	0.9	300	1.13	12	5501133	36
76.0	89.0 ± 1.5	0.9	350	1.81	12	1776690	1
102.0	115.0 ± 1.5	0.9	400	2.65	12	1776700	1
127.0	141.0 ± 1.5	0.9	500	3.46	12	1973590	1
152.0	166.0 ± 1.5	0.9	600	4.23	12	1776710	1
178.0	191.0 ± 1.5	0.9	700	4.95	12	2303130	12
204.0	219.0 ± 1.5	0.9	800	6.45	12	1776720	1

Tolerance on length: $\pm 1\%$ (ISO 1307 Standard).

Digital version



WWW.TRELLEBORG.COM/FLUIDHANDLING