

# DIAMONDSIL (ST)

## Silicone



### SILICONE SHEETING FOOD QUALITY HIGH PERFORMANCE

#### FEATURES

Transparent food grade silicone, meeting regulation (EC) 1935/2004 (European legislation) and FDA classification (American legislation).  
Volume resistivity  $> 10^{12} \Omega \cdot m$ .  
Surface resistivity  $> 10^{13} \Omega$ .

#### REGULATIONS

- Meeting european regulations (EC) n° 1935/2004 and 2023/2006
- The material is in compliance with FDA 21 CFR Part. 177. Indirect Food Additives: Polymers. Sec 177.2600 Rubber articles intended for repeated use for contact with aqueous food
- IANESCO certificate (Institut français de Poitiers)
- Tested and qualified by BNIC (Bureau National Interprofessionnel du Cognac)
- Quality certificate available under request

#### APPLICATIONS

Gaskets or washers cutting and manufacturing of pieces for general industrial applications in contact with:

- foodstuffs
- water
- detergents
- diluted acids
- strong non oxidant acids

#### ADVANTAGES

- Talcum-free, clean surface free of dust
- Time saver for cleaning and adhesive process
- Very good resistance to ozone, UV light, weathering and ageing
- Excellent temperature resistance (-60/+230°C)
- Good ratio quality/price

#### BENEFITS

- Performance
- Legality
- Food safety
- Hygiene, cleanliness
- Long life


#### MAINTENANCE RECOMMENDATION

Always follow manufacturer warnings and instructions when using any cleaning product.

#### MECHANICAL, PHYSICAL AND CHEMICAL PROPERTIES

Measured characteristics		Standard	Value	
<b>MECHANICAL</b>				
Rubber compound - transparent			Silicone	S6A0
Density			1.20 ±0.05	g/cm <sup>3</sup>
Hardness		ASTM D2240	60 ±5	Shore A
Tensile strength		ISO 37	≥10.0	MPa
Elongation at break		ISO 37	≥500	%
Tear resistance		ISO 34-1	≥20	N/mm
Compression set after 24h at 150°C		ISO 815-1	≤30	%
<b>TEMPERATURE</b>				
Working temperature			-60/+230	°C
<b>AGEING</b>				
Ozone resistance		-	Very good	
<b>CHEMICAL RESISTANCE</b>				
Diluted acids and bases	Concentrated acids and bases	Ozone	Oils and hydrocarbons	
Good	Medium	Very good	Medium	
<b>IDENTIFICATION</b>				
Branding	Without.			
Packaging	Thickness ≤6mm rolled on cardboard tube Ø 80mm. Thickness >6mm in roll.			
Wrapping	White polyethylene film.			
Labelling	Self-adhesive label indicating product name, dimensions, area in m <sup>2</sup> , nominal weight, and product code to allow product traceability.			

Unless typographical error, information and figures of our technical datasheet are based on our experience and laboratory tests according to international standards. This data is intended to be used as a guideline only. Material performance depends on the conditions of use and the final application.

Silicone	SILICONE SHEETING	DIAMONDSIL (ST)			
THICKNESS mm	WIDTH mm	LENGTH m	WEIGHT kg/m <sup>2</sup>	SIDES FINISH	
1±0.2	1200±2%	10±2%	1.2	2 SMOOTH SIDES	
1.5±0.25	1200±2%	10±2%	1.8	2 SMOOTH SIDES	
2±0.3	1200±2%	10±2%	2.4	2 SMOOTH SIDES	
3±0.3	1200±2%	10±2%	3.6	2 SMOOTH SIDES	
4±0.4	1200±2%	10±2%	4.8	2 SMOOTH SIDES	
5±0.4	1200±2%	10±2%	6	2 SMOOTH SIDES	
6±0.5	1200±2%	5±2%	7.2	2 SMOOTH SIDES	

