

MULTIDIAL UPE



FOOD & BEVERAGE

Food industry
Transfer



APPLICATIONS

Suitable for suction or discharge of any aqueous, acidic and oily foodstuffs such as milk, juices, wine, beer, brandies and spirits, vegetable oils.

Designed for:

- processing plants,
- loading or unloading bays from road and rails tankers.

ADVANTAGES

- † Food grade UPE inner tube resisting most commonly used chemical cleaning, even at high concentration/temperatures.
- † Can also be cleaned with steam up to +130°C for 30 minutes.
- † Odourless and tasteless inner tube material.
- † Non-marking, abrasion resistant cover.
- † Contains no phthalate.

TECHNICAL DESCRIPTION

Inner tube: food grade UPE (ultra high molecular weight polyethylene), white, smooth.

Reinforcement: synthetic textile with embedded steel helix.

Cover: weather resistant EPDM, blue, fabric impression.

Temperature range: -30°C to +100°C.

STANDARD/APPROVAL

EU regulations No. 1935/2004, 2023/2006, 10/2011.



FDA regulation No. 21 CFR 177.1520.



COUPLINGS/FITTINGS

Specially designed fittings are available, please contact us for further information in order to get optimum connections.

COMPLEMENTARY INFORMATION

Please refer to our cleaning guidelines, available upon request and from our website.

UPE



FDA




TRELLEBORG

MULTIDIAL UPE

MULTIDIAL UPE



FDA



**FOOD & BEVERAGE****MULTIDIAL UPE**

ID mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	MAX. VACUUM bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK () or min. order m
25.0 -0/+1	36.0 ±1.0	10	30	0.9	80	0.88	20	5513995	
25.0 -0/+1	36.0 ±1.0	10	30	0.9	80	0.88	40	5513996	
32.0 -0/+1	43.0 ±1.0	10	30	0.9	100	1.06	40	5514149	
38.0 -0/+1	49.0 ±1.0	10	30	0.9	120	1.26	20	5513997	
38.0 -0/+1	49.0 ±1.0	10	30	0.9	120	1.26	40	5513998	
51.0 -0/+1	63.5 ±1.5	10	30	0.9	160	1.7	20	5513999	
51.0 -0/+1	63.5 ±1.5	10	30	0.9	160	1.7	40	5514000	
63.0 -0/+1	75.0 ±1.5	10	30	0.9	200	2.39	20	5514001	
63.0 -0/+1	75.0 ±1.5	10	30	0.9	200	2.39	40	5514002	
76.0 -0/+1	89.0 ±1.5	10	30	0.9	250	3.26	20	5514003	
76.0 -0/+1	89.0 ±1.5	10	30	0.9	250	3.26	40	5514004	
100.0 -0/+1	114.0 ±1.5	10	30	0.9	400	4.49	20	5514005	
100.0 -0/+1	114.0 ±1.5	10	30	0.9	400	4.49	40	5514006	

Tolerance on length: ±1% (ISO 1307 Standard).

**TRELLEBORG**