



RF48 SBR



SBR SHEETING STANDARD LEVEL QUALITY

FEATURES

Standard SBR for general purpose use.

APPLICATIONS

Gaskets or washers cutting and manufacturing of pieces for general industrial purpose applications in contact with:

- water (maximum temperature +70°C)
- oil free compressed air

ADVANTAGES

- Flexible
- Good ageing resistance
- Good low temperature resistance
- Good ratio quality/price


BENEFITS

- Reliability
- Economy

MECHANICAL, PHYSICAL AND CHEMICAL PROPERTIES

Measured characteristics		Standard	Value	
MECHANICAL				
Rubber compound - black			SBR	I
	Density		1.35 ±0.05	g/cm³
	Hardness	ASTM D2240	65 ±5	Shore A
	Tensile strength	ISO 37	≥4	MPa
	Elongation at break	ISO 37	≥200	%
	Tear resistance	ISO 34-1	≥15	N/mm
	Compression set after 22h at 70 °C	ISO 815-1	≤30	%
TEMPERATURE				
	Working temperature		-25/+70	°C
CHEMICAL RESISTANCE				
Diluted acids and bases	Concentrated acids and bases	Ozone	Oils and hydrocarbons	
Very good	Good	Good	Non suitable	
IDENTIFICATION				
Branding	Without.			
Packaging	Thickness ≤6mm rolled on cardboard tube Ø 80mm. Thickness >6mm in roll.			
Wrapping	Black polyethylene film.			
Labelling	Self-adhesive label indicating product name, dimensions, area in m2, nominal weight, and product code to allow product traceability.			

Unless typographical error, information and figures of our technical datasheet are based on our experience and laboratory tests according to international standards. This data is intended to be used as a guideline only. Material performance depends on the conditions of use and the final application.

SBR	SBR SHEETING	RF48			
THICKNESS mm	WIDTH mm	LENGTH m	WEIGHT kg/m ²	SIDES FINISH	OPTION (ply)
1±0.2	1400±2%	20±2%	1.35	2 SMOOTH SIDES	
1.5±0.25	1400±2%	15±2%	2.02	2 SMOOTH SIDES	
2±0.3	1400±2%	15±2%	2.7	2 SMOOTH SIDES	1P
2±0.3	1400±2%	15±2%	2.92	2 SMOOTH SIDES	
3±0.3	1400±2%	10±2%	4.05	2 SMOOTH SIDES	2P
3±0.3	1400±2%	10±2%	4.05	2 SMOOTH SIDES	
3±0.3	1400±2%	10±2%	4.05	2 SMOOTH SIDES	1P
4±0.4	1400±2%	10±2%	5.4	2 SMOOTH SIDES	
4±0.4	1400±2%	10±2%	5.4	2 SMOOTH SIDES	1P
4±0.4	1400±2%	10±2%	5.4	2 SMOOTH SIDES	2P
5±0.4	1400±2%	10±2%	6.75	2 SMOOTH SIDES	1P
5±0.4	1400±2%	10±2%	6.75	2 SMOOTH SIDES	2P
5±0.4	1400±2%	10±2%	6.75	2 SMOOTH SIDES	
6±0.5	1400±2%	10±2%	8.1	2 SMOOTH SIDES	
6±0.5	1400±2%	10±2%	8.1	2 SMOOTH SIDES	2P
6±0.5	1400±2%	10±2%	8.1	2 SMOOTH SIDES	1P
8±0.7	1400±2%	5±2%	10.8	2 SMOOTH SIDES	2P
8±0.7	1400±2%	5±2%	10.8	2 SMOOTH SIDES	
10±1.0	1400±2%	5±2%	13.5	2 SMOOTH SIDES	
10±1.0	1400±2%	5±2%	13.5	2 SMOOTH SIDES	2P

