

CANALKLER 250 S ASSEMBLY



**CONSTRUCTION &
INFRASTRUCTURE**

Drain and sewer cleaning



APPLICATIONS

Sewer jetting and heavy duty, high pressure water cleaning.

ADVANTAGES

- | Very low sliding resistance which allows: higher cleaning efficiency, reduction of cleaning time and therefore, reduction of fuel consumption.
- | Longer lifespan thanks to the special cover compound with higher abrasion resistance.
- | Better flexibility, even at low temperatures.
- | Easy to handle and user friendly.
- | Deformation resistance.
- | Extra high strength and security due to aramide reinforcement.

TECHNICAL DESCRIPTION

Inner tube: SBR, black, smooth.

Reinforcement: aramide textile, braided.

Cover: SBR/NR, black, smooth. Very low sliding resistance.

Temperature range: -30 °C to +80 °C.

COUPLINGS/FITTINGS


All hoses are assembled with BSP female/BSP male.

All assembled hoses are pressure tested at 375bar and have an unique hose number.

COMPLEMENTARY INFORMATION

Delivered with test certificate on each factory assembled hose.

Embossed branding





ID mm	WALL THICKNESS mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK () or min. order m
13.0 ±0.5	6.3 ±0.5	25.6	250	625	70	0.45	40	5014178	
13.0 ±0.5	6.3 ±0.5	25.6	250	625	70	0.45	60	5014179	
13.0 ±0.5	6.3 ±0.5	25.6	250	625	70	0.45	80	5014180	
13.0 ±0.5	6.3 ±0.5	25.6	250	625	70	0.45	100	5014916	
13.0 ±0.5	6.3 ±0.5	25.6	250	625	70	0.45	120	5014005	
19.0 ±0.6	6.3 ±0.5	31.6	250	625	90	0.61	40	5014181	
19.0 ±0.6	6.3 ±0.5	31.6	250	625	90	0.61	80	5014182	
19.0 ±0.6	6.3 ±0.5	31.6	250	625	90	0.61	100	5014459	
19.0 ±0.6	6.3 ±0.5	31.6	250	625	90	0.61	120	5014006	
25.0 ±0.8	7.15 ±0.5	39.3	250	625	100	0.9	40	5014183	
25.0 ±0.8	7.15 ±0.5	39.3	250	625	100	0.9	50	5014874	
25.0 ±0.8	7.15 ±0.5	39.3	250	625	100	0.9	80	5014184	
25.0 ±0.8	7.15 ±0.5	39.3	250	625	100	0.9	100	5014238	
25.0 ±0.8	7.15 ±0.5	39.3	250	625	100	0.9	120	5014007	
25.0 ±0.8	7.15 ±0.5	39.3	250	625	100	0.9	150	5014461	
25.0 ±0.8	7.15 ±0.5	39.3	250	625	100	0.9	160	5014185	
25.0 ±0.8	7.15 ±0.5	39.3	250	625	100	0.9	180	5014186	
25.0 ±0.8	7.15 ±0.5	39.3	250	625	100	0.9	200	5014520	
25.0 ±0.8	7.15 ±0.5	39.3	250	625	100	0.9	240	5014733	
32.0 ±1.0	7.8 ±0.6	47.6	250	625	130	1.12	40	5014187	
32.0 ±1.0	7.8 ±0.6	47.6	250	625	130	1.12	80	5014188	
32.0 ±1.0	7.8 ±0.6	47.6	250	625	130	1.12	120	5014008	
32.0 ±1.0	7.8 ±0.6	47.6	250	625	130	1.12	150	5014466	
32.0 ±1.0	7.8 ±0.6	47.6	250	625	130	1.12	160	5014189	
32.0 ±1.0	7.8 ±0.6	47.6	250	625	130	1.12	180	5014190	
32.0 ±1.0	7.8 ±0.6	47.6	250	625	130	1.12	200	5014655	
38.0 ±1.0	8 ±0.8	54.0	250	500	155	1.35	120	5014009	

Tolerance on length: ±1% (ISO 1307 Standard).

Digital version



TRELLEBORG

WWW.TRELLEBORG.COM/FLUIDHANDLING