# ALTIPLUS

## AGRICULTURE

Farm
Spraying



## APPLICATIONS

High pressure agricultural spraying (fungicide, weed killers, insecticides, etc.).

Also suitable for paint spraying and disinfection of buildings or high pressure water discharge.

## ADVANTAGES

- A high performance hose for extra heavy duty service.
- Excellent coupling retention.
- A wide range of diameters.
- Non-marking cover.
- Good ageing and weather resistance.

## TECHNICAL DESCRIPTION


| |
|---|
| Inner tube: SBR, black, smooth. |
| Reinforcement: synthetic textile. |
| Cover: SBR, beige, with two groups of three ribs. |
| Temperature range: -30°C to +70°C. |

## STANDARD/APPROVAL

EN ISO 1401, type C for ID<16mm, type B for ID≥16mm. ISO

## COMPLEMENTARY INFORMATION

50% of the volume in each delivery will be random lengths, shortest length of 10m, at least 50% will be in fixed length mentioned in the table.



**AGRICULTURE** | **ALTIPLUS**



| ID mm | OD mm | WORKING PRESSURE bar | BURSTING PRESSURE bar | BENDING RADIUS mm | WEIGHT kg/m | LENGTH m | ARTICLE NUMBER | STOCK (ι) or min. order m |
|---|---|---|---|---|---|---|---|---|
| 8.0 ±0.5 | 16.0 ±0.6 | 60 | 240 | 40 | 0.24 | 40 | 5501371 | ¤ |
| 8.0 ±0.5 | 16.0 ±0.6 | 60 | 240 | 40 | 0.24 | 160 | 5501372 | ι |
| 9.0 ±0.5 | 17.5 ±0.6 | 60 | 240 | 40 | 0.28 | 40 | 5501373 | 1360 |
| 10.0 ±0.5 | 18.5 ±0.6 | 60 | 240 | 45 | 0.29 | 40 | 5501375 | ¤ |
| 10.0 ±0.5 | 18.5 ±0.6 | 60 | 240 | 45 | 0.29 | 50 | 5012558 | ¤ |
| 10.0 ±0.5 | 18.5 ±0.6 | 60 | 240 | 45 | 0.29 | 60 | 5012557 | ¤ |
| 10.0 ±0.5 | 18.5 ±0.6 | 60 | 240 | 45 | 0.29 | 100 | 5012556 | ¤ |
| 10.0 ±0.5 | 18.5 ±0.6 | 60 | 240 | 45 | 0.29 | 160 | 5501376 | ι |
| 10.0 ±0.5 | 18.5 ±0.6 | 60 | 240 | 45 | 0.29 | 200 | 5501377 | ι |
| 12.5 ±0.6 | 21.0 ±0.7 | 60 | 240 | 50 | 0.31 | 40 | 5501378 | ι |
| 12.5 ±0.6 | 21.0 ±0.7 | 60 | 240 | 50 | 0.31 | 80 | 5501379 | ι |
| 12.5 ±0.6 | 21.0 ±0.7 | 60 | 240 | 50 | 0.31 | 160 | 5501380 | ι |
| 16.0 ±0.7 | 26.5 ±0.8 | 40 | 160 | 80 | 0.53 | 40 | 5501381 | ι |
| 16.0 ±0.7 | 26.5 ±0.8 | 40 | 160 | 80 | 0.53 | 120 | 5501382 | 840 |

Tolerance on length: ±1% (ISO 1307 Standard). ¤ Upon availability.