

PULSOR VIB



CONSTRUCTION & INFRASTRUCTURE

Concrete vibrator



APPLICATIONS

Protection of cables between engine and vibrating head in concrete vibrators.

Used to drive compressed air stream to vibrating body.

ADVANTAGES

- † Kink resistant construction.
- † Resistance to elongation.

TECHNICAL DESCRIPTION

Inner tube: NBR/SBR, black, smooth, mild oil resistant.

Reinforcement: high tensile textile cord.


Cover: SBR/CR, black, fabric impression, abrasion, ozone and weather resistant.



Temperature range: -30°C to +80°C.



TRELLEBORG

PULSOR VIB



<div>  CONSTRUCTION & INFRASTRUCTURE </div>			PULSOR VIB						
ID mm	WALL THICKNESS mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK () or min. order m
19.0	6 ±0.5	31.0	10	40	100	0.62	40	5513544	200
25.0	7 ±0.5	39.0	10	40	125	0.95	40	5513545	200
Tolerance on length: ±1% (ISO 1307 Standard).									