SABLEX

CONSTRUCTION & INFRASTRUCTURE

Blasting and guniting



APPLICATIONS

For cleaning and shot blasting castings, metal, stone and concrete surfaces.

ADVANTAGES

- Small tolerances, therefore easy to couple.
- Longitudinally stable i.e. the length will not alter under pressure (unstable hoses result in the operator losing control when pressure is applied).
- Light weight and flexible for easy handling.
- Conductive inner tube compound gives increased safety for the operator, since there is no risk of wire breakage in use.


TECHNICAL DESCRIPTION

Inner tube: wear resistant NR, black, smooth.
Reinforcement: synthetic textile.
Cover: wear and weather resistant SBR, black, fabric impression.
Temperature range: -30°C to +70°C.
Electrical properties: conductive tube, $R<2.10^6\Omega/m$.
Special properties: abrasion resistance of tube $<40mm^3$ according to ISO 4649.



CONSTRUCTION & INFRASTRUCTURE

SABLEX



ID mm	WALL THICKNESS mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK (l) or min. order m
13.0	7 ±0.50	27.0 ±1.0	12	40	65	0.58	40	0060061	l
16.0	7 ±0.50	30.0 ±1.0	12	40	80	0.68	20	0028719	400
16.0	7 ±0.50	30.0 ±1.0	12	40	80	0.68	40	0028720	400
19.0	7.5 ±0.50	34.0 ±1.0	12	40	100	0.78	20	0028745	l
19.0	7.5 ±0.50	34.0 ±1.0	12	40	100	0.78	40	0028746	l
25.0	7 ±0.50	39.0 ±1.0	12	40	125	0.86	20	0060969	l
25.0	7 ±0.50	39.0 ±1.0	12	40	125	0.86	40	0060970	l
32.0	8 ±0.50	48.0 ±1.0	12	40	160	1.3	20	0060971	l
32.0	8 ±0.50	48.0 ±1.0	12	40	160	1.3	40	0060972	l
32.0	11 ±0.50	54.0 ±1.0	12	40	140	1.85	20	0070785	200
32.0	11 ±0.50	54.0 ±1.0	12	40	140	1.85	40	0070786	200
35.0	9 ±0.50	53.0 ±1.0	12	40	190	1.57	40	0070788	200
38.0	10 ±0.50	58.0 ±1.0	12	40	170	1.89	20	0070789	200
38.0	10 ±0.50	58.0 ±1.0	12	40	170	1.89	40	0070790	l
40.0	10 ±0.50	60.0 ±1.0	12	40	180	1.97	20	0028786	600
40.0	10 ±0.50	60.0 ±1.0	12	40	180	1.97	40	0028787	l
42.0	9 ±0.50	60.0 ±1.0	12	40	240	1.81	20	0070791	200
42.0	9 ±0.50	60.0 ±1.0	12	40	240	1.81	40	0070792	200
50.0	10 ±0.75	70.0 ±1.5	12	40	250	2.36	40	0060974	l
63.0	10 ±0.75	83.0 ±1.5	12	40	325	2.9	40	0060077	160
65.0	10 ±0.75	85.0 ±1.5	12	40	320	2.95	20	0070797	160
65.0	10 ±0.75	85.0 ±1.5	12	40	320	2.95	40	0070798	160
76.0	10 ±0.75	96.0 ±1.5	12	40	400	3.42	40	0070784	120
102.0	10 ±0.75	122.0 ±1.5	12	40	550	4.4	40	0028860	80

Tolerance on length: ±1% (ISO 1307 Standard).

Digital version

TRELLEBORG

WWW.TRELLEBORG.COM/FLUIDHANDLING