

HYDRO'K



GENERAL INDUSTRY

Multipurpose oil



APPLICATIONS

A versatile hose for industrial use.

For diesel oil, mineral oil and grease with aromatic content $\leq 50\%$.

Return hose in hydraulic system and for farming equipment.

Sea water (engine cooling) and aqueous solution.

An allround hose for oil, water, compressed air, grease, etc.

ADVANTAGES

- ¹ A multi-purpose hose to minimize inventory.
- ¹ Ozone, abrasion and oil splash resistant cover.

TECHNICAL DESCRIPTION

Inner tube: oil resistant NBR/PVC, black, smooth.

Reinforcement: synthetic textile.

Cover: oil and weather resistant NBR/SBR, black, smooth.

Temperature range: -25°C to $+100^{\circ}\text{C}$.

COMPLEMENTARY INFORMATION

Length 50m: packed in carton.

 GENERAL INDUSTRY			HYDRO'K							
ID mm	WALL THICKNESS mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	MAX. VACUUM bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK () or min. order m
5.0 ±0.4	3.25	11.5 ±0.5	16	48	0.80	30	0.12	20	0060722	☒
5.0 ±0.4	3.25	11.5 ±0.5	16	48	0.80	30	0.12	40	0060723	ℓ
5.0 ±0.4	3.25	11.5 ±0.5	16	48	0.80	30	0.12	80	0060724	☒
5.0 ±0.4	3.25	11.5 ±0.5	16	48	0.80	30	0.12	120	0060725	ℓ
6.0 ±0.4	3.5	13.0 ±0.5	16	48	0.80	35	0.15	20	0060727	☒
6.0 ±0.4	3.5	13.0 ±0.5	16	48	0.80	35	0.15	40	0060728	ℓ
6.0 ±0.4	3.5	13.0 ±0.5	16	48	0.80	35	0.15	80	0060729	ℓ
6.0 ±0.4	3.5	13.0 ±0.5	16	48	0.80	35	0.15	120	0060730	ℓ
8.0 ±0.5	3.5	15.0 ±0.6	16	48	0.80	40	0.18	20	0060732	ℓ
8.0 ±0.5	3.5	15.0 ±0.6	16	48	0.80	40	0.18	40	0060733	ℓ
8.0 ±0.5	3.5	15.0 ±0.6	16	48	0.80	40	0.18	80	0060734	ℓ
8.0 ±0.5	3.5	15.0 ±0.6	16	48	0.80	40	0.18	120	0060735	ℓ
10.0 ±0.5	3.5	17.0 ±0.6	16	48	0.80	45	0.22	20	0060737	ℓ
10.0 ±0.5	3.5	17.0 ±0.6	16	48	0.80	45	0.22	40	0060738	ℓ
10.0 ±0.5	3.5	17.0 ±0.6	16	48	0.80	45	0.22	50	0060703	☒
10.0 ±0.5	3.5	17.0 ±0.6	16	48	0.80	45	0.22	80	0060739	ℓ
10.0 ±0.5	3.5	17.0 ±0.6	16	48	0.80	45	0.22	120	0060740	ℓ
13.0 ±0.6	3.75	20.5 ±0.7	16	48	0.35	50	0.27	20	0060742	ℓ
13.0 ±0.6	3.75	20.5 ±0.7	16	48	0.35	50	0.27	40	0060743	ℓ
13.0 ±0.6	3.75	20.5 ±0.7	16	48	0.35	50	0.27	50	0060704	☒
13.0 ±0.6	3.75	20.5 ±0.7	16	48	0.35	50	0.27	80	0060744	ℓ
13.0 ±0.6	3.75	20.5 ±0.7	16	48	0.35	50	0.27	120	0060745	ℓ
15.0 ±0.7	4	23.0 ±0.8	16	48	0.35	55	0.32	20	0060746	☒
15.0 ±0.7	4	23.0 ±0.8	16	48	0.35	55	0.32	40	0060747	ℓ
15.0 ±0.7	4	23.0 ±0.8	16	48	0.35	55	0.32	80	0060748	ℓ
15.0 ±0.7	4	23.0 ±0.8	16	48	0.35	55	0.32	120	0060749	ℓ
16.0 ±0.7	4	24.0 ±0.8	16	48	0.35	60	0.34	20	0060844	☒
16.0 ±0.7	4	24.0 ±0.8	16	48	0.35	60	0.34	40	0060845	ℓ
16.0 ±0.7	4	24.0 ±0.8	16	48	0.35	60	0.34	80	0060846	ℓ
19.0 ±0.7	4.2	27.4 ±0.8	16	48	0.35	65	0.42	20	0060750	ℓ
19.0 ±0.7	4.2	27.4 ±0.8	16	48	0.35	65	0.42	40	0060751	ℓ
19.0 ±0.7	4.2	27.4 ±0.8	16	48	0.35	65	0.42	80	0060753	ℓ
25.0 ±1.0	5	35.0 ±1.1	16	48	0.35	80	0.68	20	0060755	ℓ
25.0 ±1.0	5	35.0 ±1.1	16	48	0.35	80	0.68	40	0060756	ℓ
25.0 ±1.0	5	35.0 ±1.1	16	48	0.35	80	0.68	80	0060757	ℓ

Tolerance on length: ±1% (ISO 1307 Standard).

☒ Upon availability.

Digital version



WWW.TRELLEBORG.COM/FLUIDHANDLING