

AG 1000 LT



GENERAL INDUSTRY

Exhaust gas hoses



APPLICATIONS

Extraction of exhaust gases and other hot gases from motor vehicles.

For all types of spring recoil exhaust hose reels, exhaust fume extractors and also exhaust rails for moving vehicles.

ADVANTAGES

- Extremely low weight and flexibility makes the hose especially suitable for manual handling.
- Smooth inside reduces friction losses.
- Hose lengths can be connected by screwing them together.

TECHNICAL DESCRIPTION

Inner tube: heat resistant rubberized fabric EPDM polyester, black.

Reinforcement: EPDM-coated steel, black.

Temperature range: -40°C to +150°C.

COMPLEMENTARY INFORMATION

Delivered in plastic wrapped coils.



**GENERAL INDUSTRY****AG 1000 LT**

ID mm	WALL THICKNESS mm	MAX. VACUUM bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK () or min. order m
51.0	1	0.40	65	0.42	10	5015842	60
76.0	1	0.25	95	0.6	10	5014503	80
102.0	1	0.20	110	0.74	10	5014504	50
127.0	1	0.15	130	0.91	10	5014505	90
152.0	1	0.10	140	1.1	10	5014506	60

Tolerance on length: $\pm 1\%$ (ISO 1307 Standard).

Digital version



WWW.TRELLEBORG.COM/FLUIDHANDLING