

PROJECTOR 120 WHITE



CONSTRUCTION & INFRASTRUCTURE

Spraying



APPLICATIONS

For spraying of wet mortar, mixed concrete and other wet products.

Used as a service hose between pump and nozzle in transporting plaster, grout and ready mixed concrete.

ADVANTAGES

- High working pressure.
- Light weight, flexible and easy to handle.
- Abrasion resistant tube.
- Non-staining white cover avoids traces on walls and floors.

TECHNICAL DESCRIPTION

Inner tube: wear resistant NR, black, smooth.

Reinforcement: synthetic textile.

Cover: wear and weather resistant SBR, white, fabric impression.

Temperature range: -30°C to +70°C.

Electrical properties: antistatic tube.

Special properties: abrasion resistance of tube <40mm³ according to ISO 4649.

COMPLEMENTARY INFORMATION


13.3m lengths available on request, min. order is three pieces and by multiple of three.



Other wall thickness and/or bursting pressure on request.



TRELLEBORG

PROJECTOR 120 WP 40 BAR



 CONSTRUCTION & INFRASTRUCTURE			PROJECTOR 120 WHITE						
ID mm	WALL THICKNESS mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK () or min. order m
25.0	7	39.0	40	120	200	0.85	40	59006807	1
35.0	7	49.0	40	120	280	1.13	40	59006808	200
50.0	9	68.0	40	120	410	2.22	20	59006809	1
50.0	9	68.0	40	120	410	2.22	40	59006810	1
Tolerance on length: ±1% (ISO 1307 Standard).									