

# PROJECTOR 40 WHITE



## CONSTRUCTION & INFRASTRUCTURE

Spraying



### APPLICATIONS

For spraying of mortar and mixed concrete as well as dry products.

Used as a service hose between pump and nozzle in transporting plaster, grout and ready mixed concrete.

### ADVANTAGES

- ┆ Light weight, flexible and is easy to handle.
- ┆ Abrasion resistant tube compound.
- ┆ Conductive inner tube compound gives increased safety for the operator.
- ┆ Non-staining white cover avoids traces on walls and floors.

### TECHNICAL DESCRIPTION

Inner tube: wear resistant NR, black, smooth.

Reinforcement: synthetic textile.

Cover: wear and weather resistant SBR, white, fabric impression.

Temperature range: -30°C to +70°C.


Electrical properties: conductive tube,  $R < 2 \cdot 10^6 \Omega/m$ .



Special properties: abrasion resistance of tube  $< 40mm^3$  according to ISO 4649.



TRELLEBORG

**PROJECTOR 40** WP 12 BAR



 <b>CONSTRUCTION &amp; INFRASTRUCTURE</b>			<b>PROJECTOR 40 WHITE</b>						
ID mm	WALL THICKNESS mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK ( ) or min. order m
65.0	10 ±0.75	85.0 ±1.5	12	40	320	2.79	20	59006821	∞
Tolerance on length: ±1% (ISO 1307 Standard).									∞ Upon availability.