CHEM 10 UPE SD

CHEMICALS & PHARMACEUTICALS

Chemical and corrosive products
Transfer




APPLICATIONS

Chemical resistant suction and delivery hose.

TECHNICAL DESCRIPTION

Inner tube: chemical resistant UPE (ultra high molecular weight polyethylene), white, smooth.
Reinforcement: synthetic textile with embedded steel helix.
Cover: weather and chemical resistant EPDM, green, fabric impression.
Temperature range: -30 °C to +100 °C.
Electrical properties: built-in conductive wire.



CHEMICALS & PHARMACEUTICALS

CHEM 10 UPE SD



ID mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	MAX. VACUUM bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK (l) or min. order m
13.0	25.0 ±1	10	40	0.9	65	0.47	40	5513680	l
19.0	31.0 ±1	10	40	0.9	100	0.62	40	5513681	l
25.0	37.0 ±1	10	40	0.9	125	0.79	40	5513682	l
38.0	51.0 ±1.2	10	40	0.9	200	1.21	40	5513683	l
51.0	65.0 ±1.2	10	40	0.9	250	1.87	40	5513684	l
76.0	91.0 ±1.2	10	40	0.9	400	2.92	40	5513685	160

Tolerance on length: ±1% (ISO 1307 Standard).

TRELLEBORG