

MULTI 15



GENERAL INDUSTRY

Air and water



APPLICATIONS

Compressed air and water hose in industrial applications.

TECHNICAL DESCRIPTION

Inner tube: SBR, black, smooth.

Reinforcement: synthetic textile.

Cover: SBR, black, smooth.

Temperature range: -30°C to +70°C.

6-25mm



32-63mm



 GENERAL INDUSTRY			MULTI 15					
ID mm	OD mm	WORKING PRESSURE bar	BURSTING PRESSURE bar	BENDING RADIUS mm	WEIGHT kg/m	LENGTH m	ARTICLE NUMBER	STOCK (1) or min. order m
6.0	12.0	15	45	30	0.13	40	5513820	3400
8.0	14.0	15	45	40	0.16	40	5513821	3400
10.0	16.0	15	45	50	0.19	40	5513822	3400
13.0	20.0	15	45	65	0.29	40	5513823	1
16.0	23.0	15	45	80	0.34	40	5513824	1560
19.0	26.0	15	45	90	0.39	40	5513825	1
25.0	33.0	15	45	110	0.57	40	5513826	1
32.0	42.0	15	45	320	0.77	40	5513827	120
38.0	48.0	15	45	380	0.89	40	5513828	2
51.0	63.0	15	45	510	1.43	40	5513829	1
63.0	77.0	15	45	630	2	40	5513830	120
Tolerance on length: ±1% (ISO 1307 Standard).								2 Upon availability.

